



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PD5NEWH Caseta 500W Elv Mult W/Neutral White Lutron

Catalog Number	PD5NEWH
Manufacturer	Lutron
Description	Lutron Caseta Wireless Elv+ Smart Dimmer Switch, With Phase Selectable Dimming For Led (250W), MLV (400W), Elv (500W), and Incandescent/Halogen (500W) Lighting, 120V, White
Weight per unit	0.2500 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Push-button
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Push button
Voltage Rating	120
Wattage	500

### Material, Color, and Finish

Color	White
Finish	Gloss

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	CASETA 500W ELV MULT W/NEUTRAL WHITE
extra long description	LUT PD-5NE-WH Cas?ta ELV Dimmer 250
Features	The Caseta ELV+ Smart Dimmer Switch with phase selectable dimming works with up to 250W of dimmable LED, 500W of incandescent/halogen/electronic low-voltage (ELV), or 400-Watt of magnetic low-voltage (MLV); Neutral wire connection and 10-Watt minimum load required for all load types. Out of the box, the dimmer is set to reverse phase for ELV/incandescent/halogen light loads. However, since it is phase selective, the dimmer output can be changed to forward phase for MLV lighting loads and other certain LED
Long Description	Lutron Caseta Wireless ELV+ Smart Dimmer Switch, with Phase Selectable Dimming for LED (250W), MLV (400W), ELV (500W), and Incandescent/Halogen (500W) lighting, 120V, White
Product Type	Cas?Ta Elv Dimmer 250W Led White
Special Features	Controls 250 W LED (screw-base), 500 W incandescent/halogen, 400 VA (300 W) magnetic low-voltage, 500 W electronic low-voltage, 400 W Hi-lume 1 percent 2-wire LED driver, or 3.3 A Tu-Wire fluorescent ballast loads. Simple, intuitive design with on, off and raise/lower buttons. Provides true dimming from each location with Pico wireless remotes.

## Manufacturer Information

Brand	Lutron
GTIN	00784276217699
Manufacturers Part Number	PD-5NE-WH
UPC	784276217699

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless in-wall dimmer, multi-location/single-pole

## Packaging

Carton	1
Weight Per each	0.25



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, CUL, FCC, NOM, ICC, IFTTEL