ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PD5WSDVWH Caseta DV 5A Switch 3WAY White

Lutron

Catalog Number	PD5WSDVWH
Manufacturer	Lutron
Description	Residential Meter Breaker, Button Switch, 120 to 277 V Ac, 140 W, Surface Mount, 2.94 In Length, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 0.35 LB/Ea
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Tapswitch
amperage rating	5/3
connection	Wire Leads
Contact Configuration	N-O
Contact Rating	5/3
insulation	Plastic
Material	Metal;Plastic
media	Yes
Wattage	600/1385

Material, Color, and Finish

Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75

Descriptions

Description	CASETA DV 5A SWITCH 3WAY WHITE
extra long description	LUT PD-5WS-DV-WH RF SWTCH DUAL V, 5
Features	The Lutron Caseta In-Wall Switch PRO is UL listed to work with up to 5 Amp of lighting (LED/ELV/MLV/Incandescent/Halogen), and 3 Amp of general-purpose fans. Can use either 120V or 277V. No neutral required. The Lutron minimum load capacitor (LUT-MLC) is included to assist non-neutral based digital switches in meeting minimum load requirements. This in-wall switch PRO is compatible with single pole and 3-way applications with an existing 3-way switch. For 4-way or multi-location applications, a Pico Remote
Special Features	Rated for 5 A incandescent/halogen, magnetic low-voltage, electronic low-voltage, LED/CFL, or fluorescent loads, or 3 A general purpose fans. Offers large on and off buttons. 2-wire switch ideal for retrofit applications.

Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

GTIN	00784276041133
Model	Wireless in-wall electronic switch, multi-location, 3-way, single-pole
UPC	784276041133

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Wireless in-wall electronic switch, multi-location, 3-way, single-pole

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
Mounting	WALLBOX
standard	cUL, NOM, FCC, ICC, COFETEL