



Mid-size blank wallplates

Product description

1-Gang box, 1-Gang strap, 2-Gang box



1-Gang



2-Gang


Blank - box & strap mounted

Description	Material	Color suffix	Catalog no.		
1-Gang box	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ13__	•	•
	Thermoset	A, B, LA, V, W	□ 2029__	•	•
	302/304 stainless steel	—	□ 93951	•	•
1-Gang strap	Polycarbonate	A, B, BK, LA, V, W	□ PJ14__	•	•
2-Gang box	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ23__	•	•
	Thermoset	A, LA, V, W	□ 2037__	•	•


Mid-size telephone & coax wallplates

Product description

1-gang box



1-Gang with 0.375" hole



1-Gang with 0.406" hole,
box mounted

Telephone & coax

Description	Material	Color suffix	Catalog no.		
1-Gang with 0.37" (9.5mm) hole	Thermoset	V, W	□ 2028__	•	•
	302/304 stainless steel	—	□ 93996	•	•
1-Gang with 0.40" (10.3mm) hole, box mounted	Polycarbonate	A, B, BK, LA, V, W	□ PJ11__	•	•

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant – Page Q-30


Mid-size blank wallplates

Product description

1-Gang box, 1-Gang strap, 2-Gang box





1-Gang



2-Gang


Blank - box & strap mounted

Description	Material	Color suffix	Catalog no.		
1-Gang box	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ13__	•	•
	Thermoset	A, B, LA, V, W	□ 2029__	•	•
	302/304 stainless steel	—	□ 93951	•	•
1-Gang strap	Polycarbonate	A, B, BK, LA, V, W	□ PJ14__	•	•
2-Gang box	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ23__	•	•
	Thermoset	A, LA, V, W	□ 2037__	•	•


Mid-size telephone & coax wallplates

Product description

1-gang box





1-Gang with 0.375" hole




1-Gang with 0.406" hole,
box mounted

Telephone & coax

Description	Material	Color suffix	Catalog no.		
1-Gang with 0.37" (9.5mm) hole	Thermoset	V, W	□ 2028__	•	•
	302/304 stainless steel	—	□ 93996	•	•
1-Gang with 0.40" (10.3mm) hole, box mounted	Polycarbonate	A, B, BK, LA, V, W	□ PJ11__	•	•

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

 Indicates NAFTA compliant - Page Q-30

 RoHS compliant – Page Q-30