



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PJ3W Wallplate 3G Toggle Poly Mid WH

Eaton Wiring Devices

Catalog Number	PJ3W
Manufacturer	Eaton Wiring Devices
Description	Toggle Switch Wall Plate, 3 Gang, 6.75 (W) X 4.87 (H) In, 0.080 In Thickness, Screw Mount, Polycarbonate Material, White, Gloss, 0.1500 LB
Weight per unit	0.1500 (lbs/each)
Product Category	Wall Plates & Covers

Features

cutout	0.40 In Width X 0.93 In Height
gang	3 W

Dimensions and Weight

Size	Mid, 6.75 In Width X 4.87 In Height
------	-------------------------------------

Descriptions

Construction	Warp Resistant
Description	WALLPLATE 3G TOGGLE POLY MID WH

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664751509
sub brand	Eaton Wiring
UPC	032664751509

Taxonomies, Classifications, and Categories

Category Description	RESIDENTIAL GRADE 3G PLATE
Type	COMMERCIAL

Packaging

Carton	15
Package	150
Weight Per each	0.15

Uses, Certifications, and Standards

Mounting	SCREW
----------	-------


Mid-size wallplates toggle switch

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang




4-Gang




5-Gang



6-Gang



1-Gang



2-Gang



1-Gang

Toggle switch

Gang	Material	Color suffix	Catalog no.		
1-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ1__		•
	Thermoset	A, B, LA, V, W	□ 2034__	•	•
	302/304 stainless steel	—	□ 93971	•	•
2-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ2__		•
	Thermoset	A, B, LA, V, W	□ 2039__	•	•
	302/304 stainless steel	—	□ 93972	•	•
3-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ3__		•
	Thermoset	A, B, LA, V, W	□ 2041__	•	•
	302/304 stainless steel	—	□ 93973	•	•
4-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ4__		•
	Thermoset	A, LA, V, W	□ 2054__	•	•
5-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ5__		•
6-Gang	Polycarbonate	A, B, BK, GY, LA, V, W	□ PJ6__		•

Mid-size wallplates duplex & single receptacle

Product description

1-Gang, 2-Gang

Duplex receptacle

Gang	Material	Color suffix	Catalog no.		
1-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ8__		•
	Thermoset	A, B, LA, V, W	□ 2032__	•	•
	302/304 stainless steel	—	□ 93901	•	•
2-Gang	Polycarbonate	A, B, BK, GY, LA, RD, V, W	□ PJ82__		•
	Thermoset	A, LA, V, W	□ 2050__	•	•
	302/304 stainless steel	—	□ 93902	•	•

Single receptacle

Gang	Material	Color suffix	Catalog no.		
1-Gang with 1.406" (35.712mm) hole	Thermoset	A, B, LA, V, W	□ 2031__	•	•
	302/304 stainless steel	—	□ 93991	•	•

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant - Page Q-30