


Mid-size wallplates toggle switch

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang




4-Gang




5-Gang



6-Gang



1-Gang



2-Gang



1-Gang

Toggle switch

| Gang | Material | Color suffix | Catalog no. | | |
|--------|-------------------------|----------------------------|-------------|---|---|
| 1-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ1__ | • | • |
| | Thermoset | A, B, LA, V, W | □ 2034__ | • | • |
| | 302/304 stainless steel | — | □ 93971 | • | • |
| 2-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ2__ | • | • |
| | Thermoset | A, B, LA, V, W | □ 2039__ | • | • |
| | 302/304 stainless steel | — | □ 93972 | • | • |
| 3-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ3__ | • | • |
| | Thermoset | A, B, LA, V, W | □ 2041__ | • | • |
| | 302/304 stainless steel | — | □ 93973 | • | • |
| 4-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ4__ | • | • |
| | Thermoset | A, LA, V, W | □ 2054__ | • | • |
| 5-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ5__ | • | • |
| 6-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ6__ | • | • |

Mid-size wallplates duplex & single receptacle

Product description

1-Gang, 2-Gang

Duplex receptacle

| Gang | Material | Color suffix | Catalog no. | | |
|--------|-------------------------|----------------------------|-------------|---|---|
| 1-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ8__ | • | • |
| | Thermoset | A, B, LA, V, W | □ 2032__ | • | • |
| | 302/304 stainless steel | — | □ 93901 | • | • |
| 2-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ82__ | • | • |
| | Thermoset | A, LA, V, W | □ 2050__ | • | • |
| | 302/304 stainless steel | — | □ 93902 | • | • |

Single receptacle

| Gang | Material | Color suffix | Catalog no. | | |
|------------------------------------|-------------------------|----------------|-------------|---|---|
| 1-Gang with 1.406" (35.712mm) hole | Thermoset | A, B, LA, V, W | □ 2031__ | • | • |
| | 302/304 stainless steel | — | □ 93991 | • | • |

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant – Page Q-30


Mid-size wallplates toggle switch

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang




4-Gang




5-Gang




6-Gang



1-Gang



2-Gang



1-Gang

Toggle switch

| Gang | Material | Color suffix | Catalog no. | |
|--------|-------------------------|----------------------------|-------------|-----|
| 1-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ1__ | • |
| | Thermoset | A, B, LA, V, W | □ 2034__ | • • |
| | 302/304 stainless steel | — | □ 93971 | • • |
| 2-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ2__ | • |
| | Thermoset | A, B, LA, V, W | □ 2039__ | • • |
| | 302/304 stainless steel | — | □ 93972 | • • |
| 3-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ3__ | • |
| | Thermoset | A, B, LA, V, W | □ 2041__ | • • |
| | 302/304 stainless steel | — | □ 93973 | • • |
| 4-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ4__ | • |
| | Thermoset | A, LA, V, W | □ 2054__ | • • |
| 5-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ5__ | • |
| 6-Gang | Polycarbonate | A, B, BK, GY, LA, V, W | □ PJ6__ | • |

Mid-size wallplates duplex & single receptacle

Product description

1-Gang, 2-Gang

Duplex receptacle

| Gang | Material | Color suffix | Catalog no. | |
|--------|-------------------------|----------------------------|-------------|-----|
| 1-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ8__ | • |
| | Thermoset | A, B, LA, V, W | □ 2032__ | • • |
| | 302/304 stainless steel | — | □ 93901 | • • |
| 2-Gang | Polycarbonate | A, B, BK, GY, LA, RD, V, W | □ PJ82__ | • |
| | Thermoset | A, LA, V, W | □ 2050__ | • • |
| | 302/304 stainless steel | — | □ 93902 | • • |

Single receptacle

| Gang | Material | Color suffix | Catalog no. | |
|------------------------------------|-------------------------|----------------|-------------|-----|
| 1-Gang with 1.406" (35.712mm) hole | Thermoset | A, B, LA, V, W | □ 2031__ | • • |
| | 302/304 stainless steel | — | □ 93991 | • • |

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series wallplates are UL Listed and CSA certified. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant – Page Q-30