

Project: _____ Type: _____ Prepared By: _____ Date: _____



Features and Benefits

- Replaces CFL 18W, 26W, and 32W G24q Lamps
- Ballast Compatible. Directly Compatible with Most Existing CFL Ballasts.
- Compatible with G24q / GX24q (4-pin CFL) installations
- 50,000 hour Lifespan
- Environmentally friendly, no mercury used
- UL Listed, DLC Listed
- Rated for use in enclosed and open fixtures in dry or damp locations
- 5 Year No Compromise Warranty
- Compatible with RAB specified 0-10V dimming system

Technical Specifications		
<p>Performance</p> <hr/> <p>Product Type: Compact</p> <p>Input Wattage: 9W</p> <p>Typical Lumen Output: 1000</p> <p>Efficacy: 111 lm/W</p> <p>Color Temperature: 4000K Cool White</p> <p>CRI: 82</p>	<p>L70 Lifespan: 50,000 Hours</p> <p>Dimmable: Yes</p> <p>Construction</p> <hr/> <p>Bulb Shape: PLC</p> <p>Finish: Frosted</p> <p>Base Type: G24q</p> <p>For Use Outdoors in Open Fixtures: No</p>	<p>Other</p> <hr/> <p>Equivalency: 26W Fluorescent</p> <p>Warranty (Years): RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.</p> <p>Electrical</p> <hr/> <p>Power Factor: Ballast Dependent</p> <p>Operating Temperature: -20°C - 45°C</p> <p>Input Voltage: Ballast Dependent</p>

Technical Specifications (continued)

Electrical

Operating Frequency:

Ballast Dependent

Installation

Installation Type:

Type A, Plug and Play

Installation Orientation:

Horizontal

Electrical Characteristics

THDi:

<20%

Compliance

UL Listed:

Yes

DLC Model Number:

PLC-9-H-840-DIR

CEC Status:

Lawful for sale in California

Application:

Suitable for damp locations and totally enclosed fixtures.

DLC Listed:



This product is on the Design Lights Consortium (DLC) Qualified Products List and is eligible for rebates from DLC Member Utilities. Designed to meet DLC 5.1 requirements.

DLC Product Code: PZWJK24U

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	6.5	4.9	7.1
PALLET	4032	47.2	39.4	49.6

Wiring Diagram



Dimension

