



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLF1MAM4 Mini-MRKR Tie Bulk

Panduit Corporation

Catalog Number	PLF1MAM4
Manufacturer	Panduit Corporation
Description	Panduit PLF1MA-M4Y Flag Style Marker Ties Are Used to Fasten and Identify Bundles At The Same Time. S. The Curved Tip Is Easy to Pick Up From Flat Surfaces and Allows Faster Initial Threading. Miniature Cross Section, 5.1" (130MM) Length, .76 X 1.04" (19.1 X 26.4MM) Marker Write-On Area. For Indoor Use, Made Of Nylon 6.6, Are Yellow In Color and Come In Packages Of 1000. Can Be Used With Panduit Permanent Marker Pen
Weight per unit	2.0 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	18

Dimensions and Weight

Length	5.1
Thickness	0.05
Width	0.1

Descriptions

Description	MINI-MRKR TIE BULK
extra long description	PAN PLF1MA-M4Y Pan-Ty® PLF1MA-M4Y W
Long Description	Panduit PLF1MA-M4Y Flag Style Marker Ties are used to fasten and identify bundles at the same time. s. The curved tip is easy to pick up from flat surfaces and allows faster initial threading. Miniature cross section, 5.1" (130mm) length, .76 x 1.04" (19.1 x 26.4mm) marker write-on area. For indoor use, made of Nylon 6.6, are yellow in color and come in packages of 1000. Can be used with Panduit permanent marker pen
Product Type	Pan-Ty® PLF1MA-M4Y Write-On Cable Tie, Yellow, PA6.6, 5.1"L,
Special Features	Indoor

Manufacturer Information

Brand	PANDUIT
GTIN	00074983445868
Manufacturers Part Number	PLF1MA-M4Y
UPC	074983445868

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Premium Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status	Inactive
--------	----------

Packaging

Carton	1000
--------	------

Package	10000
---------	-------

Weight Per each	2
-----------------	---

Uses, Certifications, and Standards

Application	General
-------------	---------

standard	CE Compliant, RoHS Compliant
----------	------------------------------