



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1205 N Eliseo Felix Jr. Way Suite A101  
85323-0000, AZ Avondale  
Phone: 623-259-1366  
Fax: 623-259-1367



## PLT6EHC0 Pan-Ty® PLT6EH-C0 Cable T

*Panduit Corporation*

Catalog Number	PLT6EHC0
Manufacturer	Panduit Corporation
Description	Panduit PLT6EH-C0 Lashing Cable Ties Are Ideal For Heavy Duty Applications. Extra-Heavy Cross Section, 22.2" (564MM) Length. For Indoor or Outdoor Use, Made Of Weather Resistant Nylon 6.6 With High Resistance to Ultraviolet Light, Are Black In Color and Come In Packages Of 100.
Weight per unit	0.0100 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

media	Yes
Tensile Strength	250

### Dimensions and Weight

Length	22.2
Thickness	0.08

### Descriptions

Description	PAN-TY® PLT6EH-C0 CABLE T
extra long description	PAN PLT6EH-C0 Pan-Ty® PLT6EH-C0 Cab
Long Description	Panduit PLT6EH-C0 Lashing Cable Ties are ideal for heavy duty applications. Extra-Heavy cross section, 22.2" (564mm) length. For Indoor or outdoor use, made of Weather Resistant Nylon 6.6 with high resistance to ultraviolet light, are black in color and come in packages of 100.
Product Type	Pan-Ty® PLT6EH-C0 Cable Tie, Black, Uv PA6.6, 22.2"L, 250LB,
Special Features	Indoor/Outdoor

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983541164
Manufacturers Part Number	PLT6EH-C0
UPC	074983541164

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Premium Cable Tie

### Packaging

Carton	100
Package	1000
Weight Per each	0.01



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1205 N Eliseo Felix Jr. Way Suite A101  
85323-0000, AZ Avondale  
Phone: 623-259-1366  
Fax: 623-259-1367

## Uses, Certifications, and Standards

standard

UL 62275 Compliant (Type 1, 11), UL Recognized (File #E56854),  
CSA Certified, RoHS Compliant

---