



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PRCONDUITAL1 1" Alu Plasti-Bond Conduit

Robroy/Plasti-Bond

Catalog Number	PRCONDUITAL1
Manufacturer	Robroy/Plasti-Bond
Description	Conduit, Aluminum Material; 2 Mil Red Urethane Coated (Interior), 40 Mil Gray PVC Coated (Exterior) Over Thread Finish; 10 FT; 1.063 Inch Inner Diameter; 1.395 Inch Outer Diameter; UI (Canada and Us), UI 6A, Csa C22.2 Approval; 1270 FT Standard Package
Weight per unit	0.6300 (lbs/each)
Product Category	Aluminum

Features

End Style	Threaded
Material	Aluminum
Wall Thickness	0.126 INCH

Material, Color, and Finish

Finish	2 Mil Red Urethane Coated (Interior), 40 Mil Gray PVC Coated (Exterior) Over Thread
--------	---

Dimensions and Weight

Inner Diameter	1.063 INCH
Length	10 ft
Outer Diameter	1.395 INCH



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Thread Protector Cap Color Blue; Application Protects Conductors from Mechanical Damage and Corrosive Attack While Maintaining Electrical Continuity Across the Assembled Joints
Commodity Description	Rigid Conduit Fittings - Aluminum
Description	1" ALU PLASTI-BOND CONDUIT
extra long description	ALUMINUM MATERIAL; 2 MIL RED URETHANE (INTERIOR)/40 MIL GRAY PVC (EXTERIOR)/CLEAR URETHANE COATED (THREAD) FINISH; 10 FOOT; 1.063 INCH INNER DIAMETER; 1.395 INCH OUTER DIAMETER; UL (CANADA AND US), UL 6A, CSA C22.2 APPROVAL; ANSI C80.5, ISO 9001 APPLICABLE STANDARD; 164 POUND WEIGHT; 1270 FOOT PER PACK STANDARD PACKAGE; 1 INCH TRADE SIZE; 0.126 INCH WALL THICKNESS; THREADED END STYLE; THREAD PROTECTOR COLOR BLUE; TRAVERSE AREA 0.887 SQUARE INCH; INCLUDES COUPLING
Long Description	CONDUIT, ALUMINUM MATERIAL; 2 MIL RED URETHANE COATED (INTERIOR), 40 MIL GRAY PVC COATED (EXTERIOR) OVER THREAD FINISH; 10 FT; 1.063 INCH INNER DIAMETER; 1.395 INCH OUTER DIAMETER; UL (CANADA AND US), UL 6A, CSA C22.2 APPROVAL; 1270 FT STANDARD PACKAGE
Product Type	Conduit

Manufacturer Information

Brand	PLASTIBOND
GTIN	00784011212460
Manufacturers Part Number	PRCONDUIT-AL-1
Model	PRCONDUIT-AL
UPC	784011212460

Taxonomies, Classifications, and Categories

Category Description	ALL PLASTIBOND FITTINGS
----------------------	-------------------------

Trade Size

Trade Size	1 INCH
------------	--------

Availability

Manufacturer Status	Non-Stock
minimum qty	10

Packaging

Carton	10
Package	1270
Standard Package	1270 Ft
Weight Per foot	0.63



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Approval

UL (Canada and US), UL 6A, CSA C22.2