

FEATURES & SPECIFICATIONS

INTENDED USE — Use when mounting Power Sentry PS1400DW on exterior of a fluorescent fixture. Complies with National Electrical Code provision (NEC 300) that prohibits exposed wiring.

Grommeting included to protect wiring from sharp edges of fixture knockout.


WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

atalog lumber
otes
уре

Inverter Accessories

ELA PSMK



Remote Mounting Kit

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Series

ELA PSMK Remote mounting kit for PS1400DW; two required

FEATURES & SPECIFICATIONS

INTENDED USE — Use when mounting self-diagnostics module (PSSD2) on exterior of a fluorescent fixture

Complies with National Electrical Code provision (NEC 300) that prohibits exposed wiring.

CONSTRUCTION — Constructed of 20-gauge steel. Adds 3 inches maximum to overall module length.

 $Grommeting\ included\ to\ protect\ wiring\ from\ sharp\ edges\ of\ fixture\ knockout.$


Dimensions: 3.04"L x 1.22"H x 1.26" W

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Inverter Accessories

ELA PSMKSD



Remote Mounting Kit for Self-Diagnostics

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Series

ELA PSMKSD External mounting kit for self-diagnostics module

EMERGENCY ELA-PSMK-PSMKSD-PSDMT-PSRME

FEATURES & SPECIFICATIONS

INTENDED USE — Provides simple and fast installation of PSDL3, PS1055LCP, PS1555LCP, PS1055CP FMC, PS1555CP FMC emergency drivers.

CONSTRUCTION — External mounting tray.

Adjustable bar hanging brackets.


WARRANTY — 5-year limited warranty. Complete warranty terms located at:

www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Inverter Accessories





ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Series

ELA PSDMT External mounting tray

FEATURES & SPECIFICATIONS

INTENDED USE — Provides remote mounting of Power Sentry products in air-rated plenums.

Complies with National Electrical Code Provision (NEC 300) that prohibits exposed wiring.

CONSTRUCTION — Constructed of 18-gauge steel, post-painted black.

Provides two standard 3/4" conduit knockouts and two 1/2" knockouts for test switch/pilot light mounting.

ELA PSRME Dimensions: 17" L x 3" W x 2" H

ELA PSRME IC Dimensions: 23.57" L x 3.75" W x 3.4" H

ELA PSRME and ELA PSRME IC compatible with PSQ500QD MVOLT, PS600QD MVOLT, PS1400QD MVOLT, PS730, PS750, PS1030 and PS1050, PS1055LCP.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Inverter Accessories


ELA PSRME





Remote Mounting **Enclosure**

(ELA PSRME IC)



ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Series

ELA PSRME Remote mounting enclosure

ELA PSRME IC Insulated ceiling rated remote mounting enclosure



ELA-PSMK-PSMKSD-PSDMT-PSRME