



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7604 Gateway Blvd  
77521-0000, TX Baytown  
Phone: 832-514-7819  
Fax: 832-514-7820



## PS20AC1RPL 20A 120VAC B+S Wire SP Pilot RD

*Pass & Seymour/LeGrand*

Catalog Number	PS20AC1RPL
Manufacturer	Pass & Seymour/LeGrand
Description	1-Pole Pilot Lighted Switch, Back and Side-Wire, 20A 277V
Weight per unit	0.2142 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Single pole
actuator	Toggle
amperage rating	20
Contact Rating	20Amp, 120Vac
indoor/outdoor	Indoor
insulation	False
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Universal, Incandescent, Xenon, Halogen, Fluorescent, CFL
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC
Voltage Rating	120
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120VAC B+S WIRE SP PILOT RD
extra long description	P&S PS20AC1RPL 20A 120VAC B+S WIRE
Features	Chemical Resistant
Long Description	1-Pole Pilot Lighted Switch, Back and Side-Wire, 20A 277V
Product Type	20A 120VAC B+S Wire SP Pilot Red
Special Features	Lighted when off, back & side wire, locking support heavy duty toggle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7604 Gateway Blvd  
77521-0000, TX Baytown  
Phone: 832-514-7819  
Fax: 832-514-7820

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007195842
Manufacturers Part Number	PS20AC1-RPL
UPC	785007195842

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.2142

## Uses, Certifications, and Standards

Application	Industrial Spec Grade
Enclosure	Nylon
Mounting standard	WALL CULUS, UL 498/20, FEDSPEC