



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2311 East Broadway St.  
79556-0000, TX Sweetwater  
Phone: 325-236-6381  
Fax: 325-236-6186



## PS15AC3I 15A 120/277VAC B+S Wire 3W SW Iv

*Pass & Seymour/Legrand*

Catalog Number	PS15AC3I
Manufacturer	Pass & Seymour/Legrand
Description	3-Way Toggle Switch, Back and Side-Wire, 15A 120/277V
Weight per unit	0.2300 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	15
Contact Rating	15amp, 120/277vac
indoor/outdoor	Indoor
insulation	False
Load Rating	15 A @ 120/277 VAC
Load Type	Xenon, Halogen, LED, Fluorescent, Incandescent, CFL, Universal
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Toggle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	3
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	15A 120/277VAC B+S WIRE 3W SW IV
extra long description	P&S PS15AC3I 15A 120/277VAC B+S WIR
Features	Chemical Resistant
Long Description	3-Way Toggle Switch, Back and Side-Wire, 15A 120/277V
Product Type	15A 120/277VAC B+S Wire 3W SW I
Special Features	High strength toggle, heavy duty toggle bumpers, locking support



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2311 East Broadway St.  
79556-0000, TX Sweetwater  
Phone: 325-236-6381  
Fax: 325-236-6186

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007196566
Manufacturers Part Number	PS15AC3-I
UPC	785007196566

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	SWITCH

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.23

## Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL FEDSPEC, CULUS, UL 20, FEDSPEC