

# Eaton PSG120E

Catalog Number: PSG120E

Power Supply, 120W, Single-phase, 100-240V input voltage, 24 Vdc  $\pm$  2% output voltage, 1.4A input current, 5A output current, less than 80A inrush current, 47-63 Hz, 85-264V, 120-375 Vdc, Aluminum enclosure, Heavy-duty screw terminals

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG120E
	UPC
	786685215440

Product Length/Depth	Product Height
4.76 in	4.53 in

Product Width	Product Weight
1.97 in	0.81 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year German Safety from the date of installation of the Product or eighteen (18) months from the RoHS Compliant date of shipment of the Product, whichever occurs first.	CE Marked

Certifications
UL 508
cULus/UL 60950-1
CSA Certified
IEC Rated
cUL Certified
EN Listed

## defaultTaxonomyAttributeLabel

### Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection, finger-safe cover

### Operating temperature - max

75 °C

### Operating temperature - min

-20 °C

### Power consumption

120 W

### Phase

Single-phase

### Voltage rating

85-264 Vac, 100-375 Vdc

### Frequency rating

47-63 Hz

### Enclosure material

Aluminum

### Output voltage

24 V

### Terminals

Heavy-duty screw

### Input voltage

100-240 Vac

### Series

PSG

### Rated operational current

7.5 A surge

Less than 80 A inrush

5 A output

1.4 A input

## Resources

### Brochures

[Eaton's PSG Series Power Supplies](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Drawings

[PSG120E AutoCAD 2D Footprint \(mm\)](#)

### Installation instructions

[Installation Instructions for PSG120E Power Supply](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - PSG120E](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton PSG120E

Catalog Number: PSG120E

Power Supply, 120W, Single-phase, 100-240V input voltage, 24 Vdc  $\pm$  2% output voltage, 1.4A input current, 5A output current, less than 80A inrush current, 47-63 Hz, 85-264V, 120-375 Vdc, Aluminum enclosure, Heavy-duty screw terminals

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG120E
	UPC
	786685215440

Product Length/Depth	Product Height
4.76 in	4.53 in

Product Width	Product Weight
1.97 in	0.81 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year German Safety from the date of installation of the Product or eighteen (18) months from the RoHS Compliant date of shipment of the Product, whichever occurs first.	CE Marked

Certifications
UL 508
cULus/UL 60950-1
CSA Certified
IEC Rated
cUL Certified
EN Listed

## defaultTaxonomyAttributeLabel

### Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection, finger-safe cover

### Operating temperature - max

75 °C

### Operating temperature - min

-20 °C

### Power consumption

120 W

### Phase

Single-phase

### Voltage rating

85-264 Vac, 100-375 Vdc

### Frequency rating

47-63 Hz

### Enclosure material

Aluminum

### Output voltage

24 V

### Terminals

Heavy-duty screw

### Input voltage

100-240 Vac

### Series

PSG

### Rated operational current

7.5 A surge

Less than 80 A inrush

5 A output

1.4 A input

## Resources

### Brochures

[Eaton's PSG Series Power Supplies](#)

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Drawings

[PSG120E AutoCAD 2D Footprint \(mm\)](#)

### Installation instructions

[Installation Instructions for PSG120E Power Supply](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - PSG120E](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)