



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827



PT2097HGI Self Test Plugtail Gfci HG Recp 20A Iv

Pass & Seymour/LeGrand

Catalog Number	PT2097HGI
Manufacturer	Pass & Seymour/LeGrand
Description	Plugtail Registered Hospital-Grade 20A Self-Test Gfci Receptacle. Self-Test Gfci Technology - Conducts An Automatic Test Every Three Seconds, Ensuring It'S Always Ready to Protect. Plugtail Registered Devices and Connectors Mean That Device Installation Is The Same Regardless Of Skill Level Of The Installer. The UI-Listed Connectors Are Keyed to Ensure Proper Wiring Installation Into Each Receptacle.
Weight per unit	0.2450 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

actuator	Control Circuit
amperage rating	20
connection	Built-in Connector
indoor/outdoor	Indoor
interrupt rating	4 to 6 mA
Material	Thermoplastic
media	Yes
Number of Wires	3
Outlet Type	GFCI, Hospital Grade
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Height	4.2
Length	1.03
Width	1.73



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street
72209-0000, AR Little Rock
Phone: 501-565-1785
Fax: 501-565-0827

Descriptions

Description	SELF TEST PLUGTAIL GFCI HG RECP 20A IV
extra long description	P&S PT2097HGI SELF TEST PTAIL GFCI
Features	Self-Test
Long Description	PlugTail Registered Hospital-Grade 20A Self-Test GFCI Receptacle. Self-test GFCI Technology - conducts an automatic test every three seconds, ensuring it's always ready to protect. PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.
Product Type	Self Test Ptail Gfci HG Rec 20A Iv
Special Features	Pass & Seymour invented the GFCI receptacle, and at Legrand, we're constantly reinventing it to ensure the highest level of safety possible. From the most advanced self-testing device to audible alarms to nightlight combos, we're continuously resetting the bar on GFCI innovation and safety.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007048056
Manufacturers Part Number	PT2097-HGI
UPC	785007048056

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.245

Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
Operating Temperature	-35°C to +66°C
standard	CULUS, cULus, UL Listed, FSUL