



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 S 78th St.  
33619-0000, FL Tampa  
Phone: 813-502-0060  
Fax: 000-000-0000



## PT5362W Duplex Recp Spec GRD 20A 125V WH

*Pass & Seymour/Legrand*

Catalog Number	PT5362W
Manufacturer	Pass & Seymour/Legrand
Description	Plugtail Registered Spec Grade Receptacles, 20A, 125V Plugtail Registered Devices and Connectors Mean That Device Installation Is The Same Regardless Of Skill Level Of The Installer. The UI-Listed Connectors Are Keyed to Ensure Proper Wiring Installation Into Each Receptacle.
Weight per unit	0.2300 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
Number of Wires	3
Outlet Type	STRAIGHT BLADE
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	DUPLEX RECP SPEC GRD 20A 125V WH
extra long description	P&S PT5362W DUP RECEPT SPEC GRADE 2
Features	Single Piece Plated Steel Mounting Strap
Long Description	PlugTail Registered Spec Grade Receptacles, 20A, 125V PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.
Product Type	Dup Recept Spec Grade 20A/125V W
Special Features	Crimped & welded contacts, no exposed terminals, finger safe application



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 S 78th St.  
33619-0000, FL Tampa  
Phone: 813-502-0060  
Fax: 000-000-0000

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007091724
Manufacturers Part Number	PT5362-W
UPC	785007091724

## Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	100
Weight Per each	0.23

## Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	5-15R
Operating Temperature	-40°-60°C
standard	CULUS, UL 498, FEDSPEC