



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6112 42nd Street  
79407-0000, TX Lubbock  
Phone: 806-698-6329  
Fax: 806-698-6805



## **PV810RTY Pan-Term PV8-10R-Ty Ring Terminal, Red, Vinyl, 8** *Panduit Corporation*

Catalog Number	PV810RTY
Manufacturer	Panduit Corporation
Description	The PV8-10R-Ty Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0089 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	8

### **Material, Color, and Finish**

Color	Red
Finish	Tinned

### **Dimensions and Weight**

Size	#10
------	-----

### **Descriptions**

Description	PAN-TERM PV8-10R-TY RING TERMINAL, RED, VINYL, 8
extra long description	PAN PV8-10R-TY Pan-Term® PV8-10R-TY
Long Description	The PV8-10R-TY Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV8-10R-Ty Ring Terminal, Red, Vinyl, 8 Awg, #10 S

### **Manufacturer Information**

Brand	Panduit®
GTIN	00074983421176
Manufacturers Part Number	PV8-10R-TY
UPC	074983421176

### **Taxonomies, Classifications, and Categories**

Type	Ring Terminal
------	---------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6112 42nd Street  
79407-0000, TX Lubbock  
Phone: 806-698-6329  
Fax: 806-698-6805

## Packaging

Carton ..... 200

Weight Per each ..... 0.0089

## Uses, Certifications, and Standards

Enclosure ..... Ring shape

Mounting ..... 3/8

standard ..... cULus Listed 587H E52164, CSA Certified LR31212

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)