



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV814RTY 8AWG 1/4"STD Red Insld Ring TRML

*Panduit Corporation*

Catalog Number	PV814RTY
Manufacturer	Panduit Corporation
Description	The PV8-14R-Ty Pan-Term® Terminal Is A Vinyl Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.0086 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	8

### Material, Color, and Finish

Color	Red
Finish	Tinned

### Dimensions and Weight

Size	1/4"
------	------

### Descriptions

Description	8AWG 1/4"STD RED INSLTD RING TRML
extra long description	PAN PV8-14R-TY Pan-Term® PV8-14R-TY
Long Description	The PV8-14R-TY Pan-Term® Terminal is a vinyl insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® PV8-14R-Ty Ring Terminal, Red, Vinyl, 8 Awg, 1/4"

### Manufacturer Information

Brand	Panduit®
GTIN	00074983422012
Manufacturers Part Number	PV8-14R-TY
UPC	074983422012

### Taxonomies, Classifications, and Categories

Type	Ring Terminal
------	---------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty ..... 200

## Packaging

Carton ..... 200

Weight Per each ..... 0.0086

## Uses, Certifications, and Standards

Enclosure ..... Ring shape

Mounting ..... 3/8

standard ..... cULus Listed 587H E52164, CSA Certified LR31212

Temperature Rating ..... 221 Degrees Fahrenheit (105 Degrees Celsius)