ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



PVC106 2-1/2" PVC ENTR CAP

ARLINGTON INDUSTRIES

Catalog Number	PVC106
Manufacturer	ARLINGTON INDUSTRIES
Description	PVC Entrance cap for rigid, IMC, EMT, Rigid PVC. Trade Size 2-1/2". Mast Size 2-1/2". Wire Holes four at .875.
Weight per unit	1.6 (lbs/each)
Product Category	PVC Conduit Fittings & Accy

Features

Media	Yes

Material, Color, and Finish

Color	Gray

Dimensions and Weight

Height	9.79
Hub Size	2
Length	7.62
Width	5.885

Descriptions

Description	2-1/2" PVC ENTR CAP
Long Description	PVC Entrance cap for rigid, IMC, EMT, Rigid PVC. Trade Size 2-1/2". Mast Size 2-1/2". Wire Holes four at .875.
Product Type	2-1/2" PVC Entrance Cap
Extra Long Description	ARL PVC106 2-1/2" PVC ENTRANCE CAP

Manufacturer Information

Brand	Arlington Industries ARLINGTON
GTIN	00018997125125
Manufacturers Part Number	PVC106
UPC	801230

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Push-In Connector

Packaging

Carton	1
Weight Per Each	1.6 (lbs/each)

Uses, Certifications, and Standards

Application	New work and Retrofit
Standard	cULus

NEW
more on reverse

Entrance Caps *for Rigid, IMC, EMT and PVC*

New Sizes and a Combo Style That Saves $$$!



Catalog Number	UPC/DEI/NAED Mfg. #018997	Trade Size	Clamp-on Entrance Cap for Rigid, IMC, EMT, PVC
PVC106	12512	2-1/2	
PVC109	12513	3, 3-1/2, 4	Combo style w/ adapter sleeves for 3" and 3-1/2"

NEW! SAVE $$$

See reverse for Arlington's complete line of entrance caps.

Patent pending

Whatever your entrance cap needs, Arlington has one that fits the bill.

We have two new sizes in our line of PVC Entrance Caps! In addition to the 1/2" to 2" trade sizes, we now offer a 2-1/2" cap and the combo 3" • 3-1/2" • 4".

As for clamp-on styles, we offer 1/2" to 4" caps to fit rigid, EMT and PVC.

PVC109, our new combo style is the same size as a 3" to 4" metal entrance cap, but it costs the same as a 3" PVC cap. It saves money and the hassle of stocking extra inventory because it works on three conduit sizes – 3", 3-1/2" and 4".

Priced as a 3", the (supplied) adapter sleeves allow the 4" size to fit a 3" or 3-1/2" conduit.

Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Entrance Caps *for Rigid, IMC, EMT and PVC*


Arlington has an Entrance Cap to fit your needs.



PVC100 thru PVC104



PVC105 PVC106 PVC129




PVC109 w/ adapter sleeves


NEW!

PVC for rigid • IMC • EMT • Rigid PVC. 1/2" to 2" sizes include adapter sleeve for EMT.

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	TRADE SIZE	STD PKG	DIM A	DIM B
PVC100	73100	1/2	25	2.625	2.900
PVC101	73101	3/4	25	3.340	3.150
PVC102	73102	1	20	3.340	3.360
PVC103	73103	1-1/4	10	4.125	3.530
PVC104	73104	1-1/2	10	4.145	3.530
PVC105	73105	2	5	7.790	6.660
PVC106	**12512**	**2-1/2**	**1**	**9.790**	**7.620**
PVC109	**12513**	**3, 3-1/2, 4**	**1**	**12.650**	**9.070**
PVC129	73129	2-1/2 Mast	1	7.750	6.660




PVC100 - PVC104



PVC105 - PVC129






Clamp-on Style for rigid • IMC • EMT

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	TRADE SIZE	UNIT PKG	STD PKG	DIM A	DIM B	HOLE SIZES
140	00140	1/2	10	10	2.60	2.68	(4).30
141	00141	3/4	10	10	2.72	3.80	(2).38 (3).40
142	00142	1	10	10	3.11	3.32	(2).44 (3).50
143	00143	1-1/4	5	25	3.20	4.46	(2).42 (3).63
144	00144	1-1/2	3	15	4.34	4.85	(2).60 (3).75
145	00145	2	10	10	4.55	6.62	(2).75 (3)1.00 (1).53
146	00146	2-1/2	1	1	7.80	9.74	(3)1.31 (3).87 (1).99
147	00147	3	1	1	8.00	10.50	(3)1.31 (3).87 (1).99
148	00148	3-1/2	1	1	9.25	12.50	(3)1.73 (4)1.10
149	00149	4	1	1	9.25	12.50	(3)1.73 (4)1.10



PVC Entrance Caps with galvanized steel strap

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	TRADE SIZE	STD PKG	DIM A	DIM B	HOLE SIZES
PVC660	73660	(3) 3, 6, 4, 2	50	2.700	2.520	(2).53
PVC662	73662	(3) 1/0 to (3) 4/0	10	4.125	3.750	(2).69





Service Entrance Cable Caps Zinc Diecast

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	TRADE SIZE	STD PKG	DIM A	DIM B	DIM C	HOLE SIZES
660	00660	7/8" dia. max.	50	2.060	2.970	2.260	(2).58
662	00662	1/0 to 4/0	10	3.180	4.520	3.600	(2).80



660





Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

Distributed by

© 2007 Arlington Industries, Inc.