



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PVC8X8X4 8X8X4 PVC Junction Box

*Cantex, Inc*

Catalog Number	PVC8X8X4
Manufacturer	Cantex, Inc
Description	Cantex 5133712 Is A 8 In. X 8 In. X 4 In. Junction Box Designed to Support Electrical Devices and Fixtures As Well As Providing Protection For Wires and Terminals
Weight per unit	3.0 (lbs/each)
Product Category	PVC Bodies & Boxes

### Features

insulation	Neoprene Gasket
Material	PVC
Mounting Type	Screw

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Depth	8.625
Height	8
Size	8 in. x 8 in. x 4 in. Junction Box;Non-Applicable
Width	8

### Descriptions

extra long description	CTX 5133712 8 X 8 X 4 JUNCTION BOX
Features	CANTEX 5133712 is a 8 in. x 8 in. x 4 in. Junction Box designed to support electrical devices and fixtures as well as providing protection for wires and terminals
Long Description	CANTEX 5133712 is a 8 in. x 8 in. x 4 in. Junction Box designed to support electrical devices and fixtures as well as providing protection for wires and terminals
Product Type	8 X 8 X 4 Junction Box
Special Features	Neoprene Gasket

### Manufacturer Information

Brand	PVC & Accessories
GTIN	00088700517974
Manufacturers Part Number	5133712
UPC	088700011250

### Taxonomies, Classifications, and Categories

Category Description	PVC BOXES
Type	8 in. x 8 in. x 4 in. Junction Box;Molded Junction Box



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size	8 x 8 x 4
------------	-----------

## Packaging

Carton	5
--------	---

Weight Per each	3
-----------------	---

## Uses, Certifications, and Standards

Application	JUNCTION BOX
-------------	--------------

Mounting	zinc plated steel screws
----------	--------------------------

nema rating	1;3;3S;4;4X;5;6;6P
-------------	--------------------

standard	UL Marine Listed
----------	------------------