

Specifications



Eaton QBCAF1020

Eaton QB AFCI circuit breaker, Type QBCAF
1-inch Circuit Interrupter, Single-pole,
120/240V, 10 kAIC, Combination AFCI, 20A

General specifications

| | |
|-----------------------------|--------------------------------------|
| PRODUCT NAME | Eaton QB AFCI circuit breaker |
| CATALOG NUMBER | QBCAF1020 |
| UPC | 786685244914 |
| PRODUCT LENGTH/DEPTH | 5.1 in |
| PRODUCT HEIGHT | 1.2 in |
| PRODUCT WIDTH | 3.3 in |
| PRODUCT WEIGHT | 0.2 lb |
| CERTIFICATIONS | UL 489 |
| CATALOG NOTES | HACR rated, for use in Sumter panels |



Powering Business Worldwide

Physical Attributes

| | |
|------------------------|-----------------------|
| NUMBER OF POLES | Single-pole |
| TYPE | AFCI circuit breakers |

Performance Ratings

| | |
|-------------------------|---------|
| AMPERAGE RATING | 20 A |
| INTERRUPT RATING | 10 kAIC |

Resources

| | |
|-------------------------------|--|
| CATALOGS | Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBCAF1020 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton QBCAF1020

Eaton QB AFCI circuit breaker, Type QBCAF
1-inch Circuit Interrupter, Single-pole,
120/240V, 10 kAIC, Combination AFCI, 20A

General specifications

| | |
|-----------------------------|--------------------------------------|
| PRODUCT NAME | Eaton QB AFCI circuit breaker |
| CATALOG NUMBER | QBCAF1020 |
| UPC | 786685244914 |
| PRODUCT LENGTH/DEPTH | 5.1 in |
| PRODUCT HEIGHT | 1.2 in |
| PRODUCT WIDTH | 3.3 in |
| PRODUCT WEIGHT | 0.2 lb |
| CERTIFICATIONS | UL 489 |
| CATALOG NOTES | HACR rated, for use in Sumter panels |



Powering Business Worldwide

Physical Attributes

| | |
|------------------------|-----------------------|
| NUMBER OF POLES | Single-pole |
| TYPE | AFCI circuit breakers |

Performance Ratings

| | |
|-------------------------|---------|
| AMPERAGE RATING | 20 A |
| INTERRUPT RATING | 10 kAIC |

Resources

| | |
|-------------------------------|--|
| CATALOGS | Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - QBCAF1020 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

