

# Specifications



## Eaton QBGFEP2050

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, Bolt-on mounting, 50A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, 30 mA Trip sensitivity, QBGFEP

### General specifications

|                      |                               |
|----------------------|-------------------------------|
| PRODUCT NAME         | Eaton QB GFCI circuit breaker |
| CATALOG NUMBER       | QBGFEP2050                    |
| UPC                  | 786679145203                  |
| PRODUCT LENGTH/DEPTH | 5.8 in                        |
| PRODUCT HEIGHT       | 4.4 in                        |
| PRODUCT WIDTH        | 3 in                          |
| PRODUCT WEIGHT       | 0.9 lb                        |
| WARRANTY             | 1 year                        |
| CERTIFICATIONS       | UL 943                        |
| CATALOG NOTES        | HACR rated                    |



Powering Business Worldwide

## Physical Attributes

|                             |                              |
|-----------------------------|------------------------------|
| <b>CIRCUIT BREAKER TYPE</b> | QBGFEP                       |
| <b>MOUNTING METHOD</b>      | Bolt-on                      |
| <b>NUMBER OF POLES</b>      | Two-pole                     |
| <b>TYPE</b>                 | Ground fault circuit breaker |

## Miscellaneous

|                         |                  |
|-------------------------|------------------|
| <b>SPECIAL FEATURES</b> | Bolt-on mounting |
|-------------------------|------------------|

## Performance Ratings

|                         |                        |
|-------------------------|------------------------|
| <b>AMPERAGE RATING</b>  | 50 A                   |
| <b>INTERRUPT RATING</b> | 10 kAIC                |
| <b>TRIP TYPE</b>        | Non-Interchangeable    |
| <b>TRIP RATING</b>      | 30 mA trip sensitivity |
| <b>VOLTAGE RATING</b>   | 120/240 V              |

## Resources

|                                      |                                                                                                              |
|--------------------------------------|--------------------------------------------------------------------------------------------------------------|
| <b>CATALOGS</b>                      | <a href="#">Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1</a> |
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Eaton Specification Sheet - QBGFEP2050</a>                                                       |

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.