ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

QC2015 Type QC BRKR 2P 15A 120/240VAC Max 10kaic

Eaton Corp

Catalog Number	QC2015
Manufacturer	Eaton Corp
Description	Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial Circuit Breaker, 15 A, 10 Kaic, Two-Pole, 120/240 V, Thermal-Magnetic, Cable-In/Cable-Out, QC, Non-Interchangeable
Weight per unit	0.6500 (lbs/each)
Product Category	2 Pole Din Rail Mount Circuit

Features

amperage rating	15 A
connection	Cable-in/Cable-out
dimensions	3.8000 IN X 2.2000 IN X 4.8000 IN
interrupt rating	10 kAIC
Poles	Two-pole
Trip Type	Thermal-magnetic
Voltage Rating	120/240 V

Descriptions

Description	TYPE QC BRKR 2P 15A 120/240VAC MAX 10KAIC
extra long description	ETN QC2015 QC 2P 15 AMP 120/240VAC
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker,Industrial circuit breaker,15 A,10 kAIC,Two-pole,120/240 V,Thermal-magnetic,Cable-in/cable-out,QC,Non-interchangeable
Product Type	QC 2P 15 Amp 120/240VAC Max 10kaic

Manufacturer Information

Brand	Eaton
GTIN	00786679309339
Manufacturers Part Number	QC2015
UPC	786679309339

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.65

Uses, Certifications, and Standards

Application	OtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative Energy
standard	UL Listed,CSA Certified