



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave  
76301-0000, TX Wichita Falls  
Phone: 940-257-6832  
Fax: 940-257-6833



## QC2050H Type QC BRKR 2P 50A 240VAC Max 10kaic *Eaton Corp*

Catalog Number	QC2050H
Manufacturer	Eaton Corp
Description	Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial Circuit Breaker, 50 A, 10 Kaic, Two-Pole, 240 V, Thermal-Magnetic, Cable-In/Cable-Out, QC, Non-Interchangeable
Weight per unit	0.7500 (lbs/each)
Product Category	2 Pole Din Rail Mount Circuit

### Features

connection	Cable-in/Cable-out
dimensions	3.8000 IN X 2.2000 IN X 4.9000 IN
interrupt rating	10
Poles	2
Voltage Rating	240 V - 240 V

### Descriptions

Description	TYPE QC BRKR 2P 50A 240VAC MAX 10KAIC
extra long description	ETN QC2050H TYPE QC BREAKER 2P 50A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 50 A, 10 kAIC, Two-pole, 240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable
Product Type	Type QC Breaker 2P 50A 240VAC Max 10kaic

### Manufacturer Information

Brand	Eaton
GTIN	00786679309650
Manufacturers Part Number	QC2050H
UPC	786679309650

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	0.75



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave  
76301-0000, TX Wichita Falls  
Phone: 940-257-6832  
Fax: 940-257-6833

## Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy  
Generation - Conventional Energy - Conventional Energy  
Datacenters - IT Space: CI and Hyper Converged  
Other Marine Vessels and Equipment - Marine Vessels and Equipment - Other

standard

CSA Certified, UL Listed