



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QC2050H Type QC BRKR 2P 50A 240VAC Max 10kaic *Eaton Corp*

Catalog Number	QC2050H
Manufacturer	Eaton Corp
Description	Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial Circuit Breaker, 50 A, 10 Kaic, Two-Pole, 240 V, Thermal-Magnetic, Cable-In/Cable-Out, QC, Non-Interchangeable
Weight per unit	0.7500 (lbs/each)
Product Category	2 Pole Din Rail Mount Circuit

Features

connection	Cable-in/Cable-out
dimensions	3.8000 IN X 2.2000 IN X 4.9000 IN
interrupt rating	10
Poles	2
Voltage Rating	240 V - 240 V

Descriptions

Description	TYPE QC BRKR 2P 50A 240VAC MAX 10KAIC
extra long description	ETN QC2050H TYPE QC BREAKER 2P 50A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 50 A, 10 kAIC, Two-pole, 240 V, Thermal-magnetic, Cable-in/cable-out, QC, Non-interchangeable
Product Type	Type QC Breaker 2P 50A 240VAC Max 10kaic

Manufacturer Information

Brand	Eaton
GTIN	00786679309650
Manufacturers Part Number	QC2050H
UPC	786679309650

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Renewable Energy - Alternative Energy
Generation - Conventional Energy - Conventional Energy
Datacenters - IT
Space: CI and Hyper Converged
Other
Marine Vessels and Equipment - Marine Vessels and Equipment - Other

standard

CSA Certified,UL Listed