



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QDCAST1B 54W Led Quadcast Canopy 4K 5106LM

*Cooper Lighting Solutions*

Catalog Number	QDCAST1B
Manufacturer	Cooper Lighting Solutions
Description	00080083632749 0080083 080083632749 08008363274 63274 QDCAST1B Cooper Lighting Canopy/Garage 120-277V, Gray Cooper Lighting QDCAST1B Cooper Lighting QDCAST1B Eaton / Cooper Lighting QDCAST1B Eaton Cooper Lighting QDCAST1B Eaton Cooper Lighting QDCAST1B Halo - Cooper Lighting QDCAST1B Lumark Outdoor Qdcast1b
Weight per unit	8.8 (lbs/each)
Product Category	Led Parking Lighting

### Features

amperage rating	0.48A/0.21A
Ballast Type	N/A
Lamp Type	LED
Material	Steel
Number of Lamps	1
Voltage Rating	120 to 277

### Material, Color, and Finish

Style	(blank)
-------	---------

### Descriptions

Description	54W LED QUADCST CNPY 4K 5106LM
Long Description	00080083632749 0080083 080083632749 08008363274 63274 QDCAST1B Cooper Lighting CANOPY/GARAGE 120-277V, GRAY Cooper Lighting QDCAST1B Cooper Lighting QDCAST1B Eaton / Cooper Lighting QDCAST1B Eaton Cooper Lighting QDCAST1B Eaton Cooper Lighting QDCAST1B HALO - COOPER LIGHTING QDCAST1B Lumark Outdoor QDCAST1B
Product Type	Quadcast, Canopy/Garage 120-277V, Gray
Special Features	Patented, heavy-duty, low-profile 3.5 , two-piece steel housing

### Manufacturer Information

Brand	LUMARK OUTDOOR
GTIN	00080083632749
Manufacturers Part Number	QDCAST1A
sub brand	QD Quadcast
UPC	080083632749



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	Parking/Canopy

## Availability

Manufacturer Status	Inactive
Status	Inactive

## Packaging

Carton	1
Weight Per each	8.8

## Uses, Certifications, and Standards

Application	lighting
Mounting	SURFACE/PENDANT
standard	UL/cUL Listed - Wet Location;DLC Qualified;IP66 Rated;3G Vibration Rated;ASHRAE Compliant;California Title 24