

# Eaton R5B3080U

Catalog Number: R5B3080U

Eaton rotary disconnect switch, 80 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



Photo is representative

## General specifications

Product Name

Eaton rotary disconnect switch

UPC

786685402901

Product Height

3.72 in

Product Weight

0.5 lb

Catalog Number

R5B3080U

Product Length/Depth

2.57 in

Product Width

2.07 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CCC Marked

Certifications

EN Listed  
UL 508  
IEC Rated  
CSA Certified

Catalog Notes

Suitable as motor disconnect

## Physical Attributes

### Number of poles

Three-pole

### Series

R5

## Performance Ratings

### Amperage Rating

80A

### Voltage rating

600 V

## Miscellaneous

### Product Category

Rotary Switch

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[R5B30\\_U 2D Drawing Xchange](#)

[R5B30\\_U 3D Model Xchange](#)

[R5B30\\_U AutoCAD 2D Footprint](#)

[R5B30\\_U AutoCAD 2D Footprint \(mm\)](#)

[R5B30\\_U 2D PDF](#)

[R5B30\\_U 3D Inventor](#)

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - R5B3080U](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton R5B3080U

Catalog Number: R5B3080U

Eaton rotary disconnect switch, 80 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



Photo is representative

## General specifications

Product Name

Eaton rotary disconnect switch

UPC

786685402901

Product Height

3.72 in

Product Weight

0.5 lb

Catalog Number

R5B3080U

Product Length/Depth

2.57 in

Product Width

2.07 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CCC Marked

Certifications

EN Listed  
UL 508  
IEC Rated  
CSA Certified

Catalog Notes

Suitable as motor disconnect

## Physical Attributes

### Number of poles

Three-pole

### Series

R5

## Performance Ratings

### Amperage Rating

80A

### Voltage rating

600 V

## Miscellaneous

### Product Category

Rotary Switch

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[R5B30\\_U 2D Drawing Xchange](#)

[R5B30\\_U 3D Model Xchange](#)

[R5B30\\_U AutoCAD 2D Footprint](#)

[R5B30\\_U AutoCAD 2D Footprint \(mm\)](#)

[R5B30\\_U 2D PDF](#)

[R5B30\\_U 3D Inventor](#)

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - R5B3080U](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)