



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RB300AE Rhinobox Econ 50A 125/250V NEMA3R Dupx Aut *Eaton Wiring Devices*

| | |
|------------------|--|
| Catalog Number | RB300AE |
| Manufacturer | Eaton Wiring Devices |
| Description | Eaton Rhinobox Econ Power Distribution Unit, 50A, Two Devices, Weatherproof, Nema 3R, Dupx Aut, Yellow, Cold-Rolled 18 Gauge Steel, 120/240V |
| Weight per unit | 36.0 (lbs/each) |
| Product Category | Ac Power Supplies |

Dimensions and Weight

| | |
|--------|------|
| Depth | 22.2 |
| Height | 12.3 |
| Width | 16.8 |

Descriptions

| | |
|------------------------|---|
| Description | RHINOBOX ECON 50A 125/250V NEMA3R DUPX AUT |
| extra long description | EWD RB300AE RhinoBx Econ 50A125/250 |
| Features | Eaton's Arrow Hart heavy-duty RhinoBox temporary power distribution centers provide "plug and power" capability, multiple configuration options, and automatic GFCI reset for reliable temporary power. |
| Long Description | EATON RHINOBOX ECON POWER DISTRIBUTION UNIT, 50A, TWO DEVICES, WEATHERPROOF, NEMA 3R, DUPX AUT, YELLOW, COLD-ROLLED 18 GAUGE STEEL, 120/240V |
| Product Type | Rhinobox Econ 50A125/250V NEMA3R Dupx Aut |
| Special Features | RhinoBox |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00032664719752 |
| Manufacturers Part Number | RB300AE |
| UPC | 032664719752 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Miscellaneous commercial & industrial devices |
| Type | Power distribution unit |

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 36 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Ind Facilities & Factories - Facility - Other |
| environmental conditions | Weatherproof |
| standard | NOM,cETLus |