



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD11 15A SP+SP Deco Switch BR

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | RCD11 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Control Two Separate Lights or Devices From A Single Location With This Combination Switch. Designed to Emulate The Sleek Lines Of The Collection'S Paddle Switches, It Delivers Flexible, Space-Saving Control With The Sophisticated Look Of Radiant. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately. |
| Weight per unit | 0.2083 (lbs/each) |
| Product Category | Combination Devices |

Features

| | |
|-----------------------|--|
| actuator | Rocker switch |
| amperage rating | 15 |
| Contact Configuration | 15A |
| Contact Rating | 15 Amp, 120/125 VAC |
| indoor/outdoor | Indoor |
| Load Rating | 15 A @ 120/125 VAC |
| Load Type | Fluorescent, Halogen, Universal, Incandescent, Xenon, CFL, LED |
| Material | Thermoplastic |
| media | Yes |
| Mounting Type | Wall Box |
| Number of Gangs | 1 |
| Number of Switches | 2.0 |
| operating cycles | 50,000 cycles minimum, resistive, inductive, tungstun filament lamp load |
| Poles | 3-Way, 1 |
| Switch Type | Paddle |
| throw type | Single Throw |
| Voltage | 125 VAC, 120 VAC |
| Voltage Rating | 120 |
| Wall Plate Included | NO |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | SATIN |
|--------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | Depth 1.43" x Width 1.29" x Height 3.81" |
|------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 15A SP+SP DECO SWITCH BR |
| extra long description | P&S RCD11 15A SP+SP DECO SWITCH, BR |
| Features | Decorator Style, Combination, Locator Light |
| Long Description | Control two separate lights or devices from a single location with this combination switch. Designed to emulate the sleek lines of the collection's paddle switches, it delivers flexible, space-saving control with the sophisticated look of radiant. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. |
| Product Type | 15A SP+SP Deco Switch, Brown |
| Special Features | The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes. Unique "Up/Down" switches match the look and feel of radiant paddle switches. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007060188 |
| Manufacturers Part Number | RCD11 |
| UPC | 785007060188 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.2083 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Residential |
| environmental conditions | UL94 V2 |
| Mounting | BOX |
| Operating Temperature | Maximum continuous +115°C, minimum -40°C |
| standard | cULus |