



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RC2S200TPI 2-96PG17HO 120 Bal

Advance By Signify

Catalog Number	RC2S200TPI
Manufacturer	Advance By Signify
Description	00781087221822 0007810 00781087221822 78108722182 22182 RC2S Lamps RC2S200TP1 Signify Lamps RC2S200TPI Signify Lighting RC2S200TP1 Signify Lighting RC2S200TPI Signify Luminaires RC2S200TP1 Signify Luminaires RC2S200TPI Signify North America Corp RC2S200TP1 Signify North America Corp RC2S200TPI Signify RC2S200TP1 Signify RC2S200TPI Signifylamps RC2S200TP1 Signifylamps RC2S200TPI Signify?Philipslamp RC2S200TP1 Signify?Philipslamp Rc2s200tpi
Weight per unit	14.4 (lbs/each)
Product Category	Magnetic Linear Fluorescent Ba

Features

Ballast Factor	0.8
Lamp Type	T12
Number of Lamps	2
Power Factor	HIGH
start type	Rapid Start
total harmonic distortion	20
Voltage Rating	120
Wattage	200
Wire Type	SOLID

Material, Color, and Finish

Housing Material	Metal
------------------	-------

Descriptions

Description	2-96PG17HO 120 BAL
Long Description	00781087221822 0007810 00781087221822 78108722182 22182 RC2S Lamps RC2S200TP1 Signify Lamps RC2S200TPI Signify Lighting RC2S200TP1 Signify Lighting RC2S200TPI Signify Luminaires RC2S200TP1 Signify Luminaires RC2S200TPI SIGNIFY NORTH AMERICA CORP RC2S200TP1 SIGNIFY NORTH AMERICA CORP RC2S200TPI Signify RC2S200TP1 Signify RC2S200TPI SIGNIFYLAMPS RC2S200TP1 SIGNIFYLAMPS RC2S200TPI SIGNIFY?PHILIPSLAMP RC2S200TP1 SIGNIFY?PHILIPSLAMP RC2S200TPI
Product Type	Mag Ballast (2)F96T12/Vho 120V Ic Pack
Special Features	UL, CSA, RoHS



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Advance
GTIN	00781087221822
Manufacturers Part Number	RC2S200TPI
UPC	781087221822

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Magnetic Fluorescent

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	14.36

Uses, Certifications, and Standards

Application	L(2.860) x W(0.960) x H(1.000)
Frequency Rating	60