

# Specifications

## Eaton REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V



### General specifications

|                      |                                |
|----------------------|--------------------------------|
| PRODUCT NAME         | Eaton Bussmann series REN fuse |
| CATALOG NUMBER       | REN-30                         |
| UPC                  | 051712100304                   |
| PRODUCT LENGTH/DEPTH | 2 in                           |
| PRODUCT HEIGHT       | 0.56 in                        |
| PRODUCT WIDTH        | 0.56 in                        |
| PRODUCT WEIGHT       | 0.55 lb                        |
| WARRANTY             | Not Applicable                 |
| COMPLIANCES          | Not Applicable                 |

## Electrical rating

|                  |         |
|------------------|---------|
| AMPERAGE RATING  | 30 A    |
| INTERRUPT RATING | 10 kAIC |
| VOLTAGE RATING   | 250 V   |

## General information

|                  |                                           |
|------------------|-------------------------------------------|
| CLASS            | Class H                                   |
| CONNECTION       | Ferrule end x ferrule end                 |
| FUSE INDICATOR   | Non-indicating                            |
| QUANTITY         | 10                                        |
| SPECIAL FEATURES | Super lag, time lag, non current-limiting |

## Physical details

|                |          |
|----------------|----------|
| PACKAGING TYPE | Standard |
|----------------|----------|

## Resources

|                               |                                                                                                     |
|-------------------------------|-----------------------------------------------------------------------------------------------------|
| CATALOGS                      | <a href="#">Bussmann series full line catalog 1007, section 01-low voltage branch circuit fuses</a> |
|                               | <a href="#">REN-30~SUPER LAG RENEWABLE FUSE 30/250</a>                                              |
|                               | <a href="#">Bussmann series complete full line catalog no. 1007</a>                                 |
| MULTIMEDIA                    | <a href="#">Bussmann series Fuseology</a>                                                           |
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - REN-30</a>                                                  |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

