



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## REZ3S32SC35I 32W 120V Bal

*Advance By Signify*

Catalog Number	REZ3S32SC35I
Manufacturer	Advance By Signify
Description	As Easy As 1, 2, 3 Compatible With Controls From Numerous Manufacturers Without Using Separate Control Leads - Powerline Dimming Interface; Ideal For Frequent Switching Applications Such As Occupancy Sensors and Daylight Harvesting - Programmed Start Operation For Companies Looking to Make Their Fixed-Output Linear T8, 4-Pin CFL, and T5/Ho Fluorescent Systems More Cost Effective and Sustainable, Mark 10 Powerline Ballasts Provide An Easy Solution Without The Need For Additional Control Leads. Simply, (1) Re
Weight per unit	1.1 (lbs/each)
Product Category	20040218133958

### Features

Ballast Factor	0.97
Lamp Type	T8
Number of Lamps	3
Power Factor	0.99
start type	Programmed Start
total harmonic distortion	10
Voltage Rating	120
Wattage	32
Wire Type	SOLID

### Material, Color, and Finish

Housing Material	Metal
------------------	-------

### Dimensions and Weight

Height	4.65
Width	0.67



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	32W 120V BAL
extra long description	ADV REZ3S32SC35I ELE DIMMING BALLAS
Long Description	As easy as 1, 2, 3 Compatible with controls from numerous manufacturers without using separate control leads - Powerline dimming interface; Ideal for frequent switching applications such as occupancy sensors and daylight harvesting - Programmed start operation For companies looking to make their fixed-output linear T8, 4-pin CFL, and T5/HO fluorescent systems more cost effective and sustainable, Mark 10 Powerline ballasts provide an easy solution without the need for additional control leads.
	Simply, (1) re
Product Type	Ele Dimming Ballast (3) F32T8 120V
Special Features	UL, CSA, NEMA Premium, RoHS

## Manufacturer Information

Brand	Advance
GTIN	00781087106976
Manufacturers Part Number	REZ3S32SC35I
UPC	781087106976

## Taxonomies, Classifications, and Categories

Category Description	DIMMING BALLASTS
Type	Dimmable Fluorescent

## Packaging

Carton	1
Package	10
Weight Per each	1.06

## Uses, Certifications, and Standards

Application	DIMMING
Frequency Rating	60
standard	CSA certificate; UL certificate; CEC Listing; CEE Rated; NEMA Premium; RoHS Compliant