



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RH4FBL3PTC Radiant 0-10V FL/Led Dimmer TC

Pass & Seymour/Legrand

Catalog Number	RH4FBL3PTC
Manufacturer	Pass & Seymour/Legrand
Description	Dimmer Switch, 1.75 Inch W X 1.25 Inch D X 4.25 Inch H Size; Tri-Color (Ivory, White, Light Almond) Finish; 1-Pole, 3-Way Operation Type; UL (Canada and Us), Csa Approval; 120/277 Vac Voltage Rating; On/Off Preset Paddle Switch Operator Type
Weight per unit	0.4083 (lbs/each)
Product Category	Lighting Dimmers

Features

Load Type	Fluorescent/LED
Operation Type	1-Pole, 3-Way
Operator Type	On/Off Preset Paddle Switch
Voltage Rating	120/277 VAC
Wall Plate Type	Screwless

Material, Color, and Finish

Finish	Tri-Color (Ivory, White, Light Almond)
--------	--

Dimensions and Weight

Size	1.75 INCH W X 1.25 INCH D X 4.25 INCH H
------	---

Descriptions

Commodity Description	LIGHTING DIMMERS
Description	RADIANT 0-10V FL/LED DIMMER TC
Long Description	DIMMER SWITCH, 1.75 INCH W X 1.25 INCH D X 4.25 INCH H SIZE; TRI-COLOR (IVORY, WHITE, LIGHT ALMOND) FINISH; 1-POLE, 3-WAY OPERATION TYPE; UL (CANADA AND US), CSA APPROVAL; 120/277 VAC VOLTAGE RATING; ON/OFF PRESET PADDLE SWITCH OPERATOR TYPE
Product Type	Dimmer Switch

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007053319
Manufacturers Part Number	RH4FBL3-PTC
UPC	785007053319

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
----------------------	-----------------------------------

Availability

Manufacturer Status	Non-Stock
---------------------	-----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.4083

Uses, Certifications, and Standards

Approval	UL (CANADA AND US), CSA
----------	-------------------------