



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RL460WH930 4" Led Retro 30K 90CRI WHT

Cooper Lighting Solutions

Catalog Number	RL460WH930
Manufacturer	Cooper Lighting Solutions
Description	00080083690770 0080083 080083690770 08008369077 69077 RL460WH930 RL4 WH 90CRI 3000K PK, HV Cooper Lighting RL460WH930PK CooperLighting RL460WH930PK Eaton / Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK Halo - Cooper Lighting RL460WH930PK Halo - Recessed RL460WH930PK
Weight per unit	1.1 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	0.075A - 0.0875A (at 120V)
Lamp Type	LED
Voltage Rating	120
Wattage	8 W

Descriptions

Long Description	00080083690770 0080083 080083690770 08008369077 69077 RL460WH930 RL4 WH 90CRI 3000K PK, HV Cooper Lighting RL460WH930PK CooperLighting RL460WH930PK Eaton / Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK HALO - COOPER LIGHTING RL460WH930PK Halo - Recessed RL460WH930PK
Product Type	Halo RL4 WH 90CRI 3000K PK, HV
Special Features	ENERGY STAR® certified

Manufacturer Information

Brand	HALO - RECESSED
GTIN	00080083690770
Manufacturers Part Number	RL460WH930PK
sub brand	RL4 All-Purpose LED Baffle-trim Modules
UPC	080083690770

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	RL4 LED



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Status Inactive

Packaging

Carton 1

Weight Per each 1.1299

Uses, Certifications, and Standards

Application lighting

standard UL/cUL Listed 1598 Luminaire;UL Classified;cULus Listed - Damp Location;cULus Listed - Wet Location;IP65 Rated;Energy Star Certified;AIR-TITE (TM) Certified ASTM E28;California Title 24;Title 20 Compliant;IECC Compliant;EMI/RFI per FCC 47CFR Part 15 B;RoHS Compliant