



FUTURE FIT

LED KITS

CATALOG NUMBER:
KT-RKIT-2AG44-6000-8XX-VDIM



DESCRIPTION

UL 1598C Classified LED Retrofit Kit. Includes the Following Components:

(1) LED Driver, (2) Alumagroove LED Modules, (2) Lenses, Mounting Accessories (Jumper Wires, Tek Screws, Power Quick-Disconnect)



APPLICATION

Suitable for use in Troffers, Wraps, Strips, Vapor Tights, and other indoor fixture types.

PRODUCT FEATURES

Module Features

- For Use In Class 2 Lighting Systems
- High Lumen Density Design
- Completely Heat Sunked, No Additional Heat Sinking Needed to Maintain LED Lifetime
- Made with UL Recognized Components
- 2835 LED Chip Package
- Reported Life Expectancy: L70 >54,000 Hours at 85C | L90 48,000 Hours at 85C
- Calculated Life Expectancy: L70>160,000 Hours at 85C | L90 48,000 at 85C
- Beam Angle: 120 Degree
- Low Profile WAGO Push Connectors Located on Bottom of Modules to Eliminate Dark Spots on End-to-End Connections

Driver Features

- 120-277V Input, High Power Factor, 0-10V Dimming
- UL Class P
- Meets FCC Part 15 Class B (Consumer) Limit for EMI
- Over Current and Short Circuit Protection
- Class 2 Output
- Operating Temperature: -20C/-4F to 55C/131F
- THD < 20%
- DLC Premium Listed



CATALOG NUMBER:
KT-RKIT-2AG44-6000-8XX-VDIM

PERFORMANCE SPECIFICATIONS

4' LINEAR KITS, 80 CRI

KIT SPECIFICATIONS:

Dimming Type: 0-10V

Driver: (1) KTL D-40-UV-1350-VDIM-LA3

Module: (2) KTAG-44L-1400-30-8xx-RJ


Color Temp	Input Voltage	CRI	AlumaGroove Kit Catalog Number	No. of Modules	Total System Drive Current	Drive Current per Module	Total System Lumens	Total Module Power	Module Efficacy	Driver Efficiency	Total System Power	Total System Efficacy
3500K	120-277V	>80	KT-RKIT-2AG44-6000-835-VDIM	2	1350mA	675mA	6032	38W	159 lm/W	84%	45W	134 lm/W
4000K	120-277V	>80	KT-RKIT-2AG44-6000-840-VDIM	2	1350mA	675mA	6108	38W	161 lm/W	84%	45W	135 lm/W
5000K	120-277V	>80	KT-RKIT-2AG44-6000-850-VDIM	2	1350mA	675mA	6221	38W	164 lm/W	84%	45W	138 lm/W

ACCESSORIES


Lens	KTAG-44L-LENS
------	---------------

NOTE: Included

PHYSICAL SPECIFICATIONS



Side View



Without Lens

With Lens

CASE DIMENSIONS

	LENGTH	9.5"
	WIDTH	1.3"
	HEIGHT	1"
	MOUNTING	9"
	CASE STYLE	LA3



FUTURE FIT
LED KITS

CATALOG NUMBER:
KT-RKIT-2AG44-6000-8XX-VDIM

ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-RKIT-2AG44-6000-8XX-VDIM	Individually Packaged	20	Quick Ship

CATALOG NUMBER BREAKDOWN

KT-RKIT-2AG44-6000-8XX-VDIM

Keystone Technologies	Retrofit Kit	Number of Modules	Aluma Groove	Nominal Length (In.)	Nominal Lumens	80 CRI	Color Temp	0-10V Dimmable
-----------------------	--------------	-------------------	--------------	----------------------	----------------	--------	------------	----------------