

Specifications



Photo is representative



Eaton RPD4K0800

Eaton NEMA 3R enclosure. Accepts PD4, 3-Pole, 800A frame MCCB

General specifications

PRODUCT NAME	Eaton enclosed circuit breaker
CATALOG NUMBER	RPD4K0800
UPC	786689662035
PRODUCT LENGTH/DEPTH	17.5 in
PRODUCT HEIGHT	63.5 in
PRODUCT WIDTH	23 in
PRODUCT WEIGHT	120 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Power Defense Enclosure - not approved for Series C/G MCCB
GLOBAL CATALOG	RPD4K0800



Powering Business Worldwide

Product specifications

AMPERAGE RATING	800 A
ENCLOSURE	NEMA 3R
TYPE	Circuit Breaker Enclosure

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RPD4K0800
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton RPD4K0800

Eaton NEMA 3R enclosure. Accepts PD4, 3-Pole, 800A frame MCCB

Photo is representative



General specifications

PRODUCT NAME	Eaton enclosed circuit breaker
CATALOG NUMBER	RPD4K0800
UPC	786689662035
PRODUCT LENGTH/DEPTH	17.5 in
PRODUCT HEIGHT	63.5 in
PRODUCT WIDTH	23 in
PRODUCT WEIGHT	120 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Power Defense Enclosure - not approved for Series C/G MCCB
GLOBAL CATALOG	RPD4K0800



Powering Business Worldwide

Product specifications

AMPERAGE RATING	800 A
ENCLOSURE	NEMA 3R
TYPE	Circuit Breaker Enclosure

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RPD4K0800
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

