


The Armored Cable Cutting Experts Since 1973. Ask About Our Custom Tools & Automated Systems.

"BEST CUTTER ON THE MARKET"



SAVE TIME & LABOR WITH A TOP QUALITY TOOL!

For 14-2 to 10-4 AC, MC, HCF, BX and 3/8" Flex

Accessories: B-102 Replacement Blade B-107 Blade for Aluminum Casing LS-105 Lubricant Stick 101-107 Power Conversion Kit

**ROTO-SPLIT® "SUPER" RS-101A
BX CABLE ARMOR STRIPPER**

With Ergonomic Handle & Blade Storage Cartridge

- A few turns of the crank produces a clean slit through the armor casing which is then twisted and easily removed.
- Unique **quick clamping and release** of the cable. No fuss side loading.
- Preset depth of cut for BX cables to **prevent nicking of the conductors** & an adjustment screw for thin wall MC cables is provided.
- Automatic compensation for cable size variation. A must for the fastest professional job in the trade!

Order RS-101AL equipped with B-107 blade to cut aluminum casing
Order RS-101AP Power-Split screwgun driven Roto-Split

"THE POWER SWING-SAW!"



MM-175


U.S. Patents 5,611,146 & 5,806,187

A New Concept in Reciprocating Saw Accessories

Order a complete model for your reciprocating saw which includes MM-175 Vise & Adapter. Need to use on more than one saw or you just bought a different model? Contact Seatek to order the correct adapter.

MIGHTY-MITER RECIPROCATING SAW ACCESSORY

- Makes it a snap to cut square any material: round, square or rectangular tubing, wood & plastic molding, angle bar, EMT raceway, threaded rods, etc.
- The vise & clamping assembly swings up towards the reciprocating blade which cuts virtually anything perfectly square.
- Unique clamping system can be disengaged and engaged to quickly adjust the clamping jaws from 3/16" to 2".
- Using the **Mighty-Miter®** prevents the "shakes" and blades will last longer.
- Can be attached to many different reciprocating saws with no modification.



Choose the Mighty-Miter® for your Reciprocating Saw

| | |
|----------|--|
| MM-175RS | Mighty-Miter for Milwaukee® Sawzall® |
| MM-175SS | Mighty-Miter for Milwaukee® Super-Sawzall® |
| MM-175OR | Mighty-Miter for Milwaukee® Orbital-Sawzall® |
| MM-175BP | Mighty-Miter for Milwaukee® 18 Volt Sawzall® |
| MM-175DW | Mighty-Miter for DeWalt® DW-303 Saw |

All brands and product names are trademarks or registered trademarks of their respective companies

"MAKE IT EASY ON YOURSELF"



TS-190

U.S. Patent 4,865,294

TOP-SLIDE®

SUSPENDED CEILING CABLE GUIDE

- At last a low cost product to save you time and aggravation while pulling cables in plenum.
- The patented Top-Slide is designed to snap onto a ceiling tee bar.
- With two Top-Slides in place, pulling any type of cable over tee bars is a cinch, even armored cable with kinks in it.
- The Top-Slide spells the end of damaged ceiling tees, and best of all one man can do the job instead of two!

GRAB A TOP-SLIDE & SEE HOW SIMPLE IT IS TO PULL CABLES OVER THE CEILING GRID!

"GUARANTEED NO KINKS!"



U.S. Patent 4,746,099

Order FT-210 Fish Tape Puller



**THE "HINGENIOUS"
NEW CAM-ACTION HINGED
FISH TAPE PULLER**

- Two handed action has twice the pulling force, the more you pull the more it grabs!
- Stop putting kinks in your fish tape or grazing your face with your pliers.
- Precision hardened steel casting, 100% made in America, 8 oz. 11" long.
- A must for your tool box!

EASY DOES IT WITH TWICE THE PULLING FORCE!



ON THE INTERNET LOG ON TO www.SeatekCo.com - WHERE QUALITY & SMART ENGINEERING COME TO LIFE!