



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

720 S Lewis Ln
78552-0000, TX Harlingen
Phone: 956-622-4123
Fax: 956-622-4124



RWP262I 2G Radiant Screwless Wallplate Iv

Pass & Seymour/Legrand

Catalog Number	RWP262I
Manufacturer	Pass & Seymour/Legrand
Description	Designed to Complement Any Space, The Radiant Registered Collection Features Sleek, Screwless Wall Plates For Cleaner Lines and A Sophisticated Touch. Pair This Two-Gang Option With Your Preferred Combination Of Radiant Registered Switches, Dimmers, and/or Outlets For A Completed Look That'S A Step Above Ordinary.
Weight per unit	0.1217 (lbs/each)
Product Category	Wall Plates & Covers

Features

cutout	Decorator
indoor/outdoor	Indoor
insulation	Bare
media	Yes
Mounting Type	Screwless
Number of Gangs	2
orientation	Vertical
Wall Plate Type	DECORATOR

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Depth	.065
Thickness	0.065



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

720 S Lewis Ln
78552-0000, TX Harlingen
Phone: 956-622-4123
Fax: 956-622-4124

Descriptions

Construction	Plastic
Description	2G RADIANT SCREWLESS WALLPLATE IV
extra long description	P&S RWP262I RADIANT SCREWLESS WALLP
Features	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this two-gang option with your preferred combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Long Description	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this two-gang option with your preferred combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Product Type	Radiant Screwless Wallplate 2G I
Special Features	Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends. Molded of rugged .065' thick polycarbonate. One-piece subplate mounts over the device for easy retrofit and lower profile. Subplate screws align device to ensure proper positioning of the wall plate. Opening accommodates all NEMA 26 opening devices. An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007231779
Manufacturers Part Number	RWP262I
UPC	785007231779

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Wall Plate

Packaging

Carton	1
Package	6
Weight Per each	0.1217

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting	WALL MOUNT
standard	CSA, UL514, ETL