

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1011 First Place Blvd 73099-0000, OK Yukon Phone: 405-265-8424

Fax: 405-494-4041



Thickness

RWP263 3G Radiant Screwless Wallplate BN *Pass & Seymour/Legrand*

Catalog Number	RWP263	
Manufacturer	Pass & Seymour/Legrand	
Description	Designed to Complement Any Space, The Radiant Registered Collection Features Sleek, Screwless Wall Plates For Cleaner Lines and A Sophisticated Touch. Pair This Three-Gang Option With A Combination Of Radiant Registered Switches, Dimmers, and/or Outlets For A Completed Look That'S A Step Above Ordinary.	
Weight per unit	0.1633 (lbs/each)	
Product Category	Wall Plates & Covers	
Features		
cutout	Rectangular	
indoor/outdoor	Indoor	
insulation	Bare	
media	Yes	
Mounting Type	Screwless	
Number of Gangs	3	
orientation	Vertical	
Wall Plate Type	DECORATOR	
Material, Color, and Finish		
Finish	Matte	
Dimensions and Weight		
Depth	.065	

0.065



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1011 First Place Blvd 73099-0000, OK Yukon Phone: 405-265-8424 Fax: 405-494-4041

_	•		
11000	rın	tia	nc
Desc	,		· ·

Construction	Plastic
Description	3G RADIANT SCREWLESS WALLPLATE BN
extra long description	P&S RWP263 RADIANT SCREWLESS WALLPL
Features	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this three-gang option with a combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Long Description	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this three-gang option with a combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Product Type	Radiant Screwless Wallplate 3G BRN
Special Features	Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends. Molded of rugged .o65" thick polycarbonate. One-piece subplate mounts over the device for easy retrofit and lower profile. Subplate screws align device to ensure proper positioning of the wall plate. Opening accomodates all NEMA 26 opening devices. An extra 3/8" width and height than standard size wall paltes for more tolerance in covering ragged sheet rock openings.
anufacturer Information	

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007231854
Manufacturers Part Number	RWP263
UPC	785007231854

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Туре	Wall Plate

Packaging

Carton	1	
Package	6	
Weight Per each	0.1633	

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting	WALL MOUNT
standard	CSA, UL514, ETL