



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RWP262BK 2G Radiant Screwless Wallplate BK

*Pass & Seymour/Legrand*

Catalog Number	RWP262BK
Manufacturer	Pass & Seymour/Legrand
Description	Designed to Complement Any Space, The Radiant Registered Collection Features Sleek, Screwless Wall Plates For Cleaner Lines and A Sophisticated Touch. Pair This Two-Gang Option With Your Preferred Combination Of Radiant Registered Switches, Dimmers, and/or Outlets For A Completed Look That'S A Step Above Ordinary.
Weight per unit	0.1217 (lbs/each)
Product Category	Wall Plates & Covers

### Features

cutout	2 - Decorator
indoor/outdoor	Indoor
insulation	Bare
Mounting Type	Screwless
Number of Gangs	2
orientation	Vertical
Wall Plate Type	DECORATOR

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Depth	.065
Thickness	0.065



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Plastic
Description	2G RADIANT SCREWLESS WALLPLATE BK
extra long description	P&S RWP262BK RADIANT SCREWLESS WALL
Features	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this two-gang option with your preferred combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Long Description	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this two-gang option with your preferred combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Product Type	Radiant Screwless Wallplate 2G BK
Special Features	Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends. Molded of rugged .065" thick polycarbonate. One-piece subplate mounts over the device for easy retrofit and lower profile. Subplate screws align device to ensure proper positioning of the wall plate. Opening accomodates all NEMA 26 opening devices. An extra 3/8" width and height than standard size wall paltes for more tolerance in covering ragged sheet rock openings.

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007231731
Manufacturers Part Number	RWP262BK
UPC	785007231731

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Wall Plate

## Packaging

Carton	1
Package	6
Weight Per each	0.1217

## Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting standard	WALL MOUNT UL514, cULus, CSA Certified