



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln
79109-3210, TX Amarillo
Phone: 806-220-0404
Fax: 806-220-0811



RWP264 4G Radiant Screwless Wallplate BN

Pass & Seymour/Legrand

Catalog Number	RWP264
Manufacturer	Pass & Seymour/Legrand
Description	Designed to Complement Any Space, The Radiant Registered Collection Features Sleek, Screwless Wall Plates For Cleaner Lines and A Sophisticated Touch. Pair This Four-Gang Option With A Combination Of Radiant Registered Switches, Dimmers, and/or Outlets For A Completed Look That'S A Step Above Ordinary.
Weight per unit	0.1983 (lbs/each)
Product Category	Wall Plates & Covers

Features

cutout	Rectangular
indoor/outdoor	Indoor
insulation	Bare
media	Yes
Mounting Type	Screwless
Number of Gangs	4
orientation	Vertical
Wall Plate Type	DECORATOR

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Depth	.065
Thickness	0.065



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln
79109-3210, TX Amarillo
Phone: 806-220-0404
Fax: 806-220-0811

Descriptions

Construction	Plastic
Description	4G RADIANT SCREWLESS WALLPLATE BN
extra long description	P&S RWP264 RADIANT SCREWLESS WALLPL
Features	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this four-gang option with a combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Long Description	Designed to complement any space, the radiant Registered Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this four-gang option with a combination of radiant Registered switches, dimmers, and/or outlets for a completed look that's a step above ordinary.
Product Type	Radiant Screwless Wallplate 4G BRN
Special Features	Redesigned screwless wall plates feature a lower, more modern profile in keeping with today's design trends. Molded of rugged .065" thick polycarbonate. One-piece subplate mounts over the device for easy retrofit and lower profile. Subplate screws align device to ensure proper positioning of the wall plate. Opening accomodates all NEMA 26 opening devices. An extra 3/8" width and height than standard size wall paltes for more tolerance in covering ragged sheet rock openings.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007231991
Manufacturers Part Number	RWP264
UPC	785007231991

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Wall Plate

Packaging

Carton	1
Package	6
Weight Per each	0.1983

Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting standard	WALL MOUNT CSA, UL514, ETL