



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390



S100X225VAM 1.00" X 2.25" Self-Laminating Vinyl Wire Marker

Panduit Corporation

Catalog Number	S100X225VAM
Manufacturer	Panduit Corporation
Description	The S100X225VAM Die-Cut Self-Laminating Label Cassette Includes Both Label Material and Ribbon For Easy Changeover. Self-Laminating Adhesive Labels For Wire/Cable Identification Include A White Print-On Area and A Clear Overlaminates. For Use With The MP300 Printer. Vinyl. 1" X 2.25" (25.4 MM X 57.2 MM). Wire/Cable Size Range 8 - 4 Awg. Color Clear/White. 125 Labels Per Cassette. 1 Cassette Per Package.
Weight per unit	0.2040 (lbs/each)
Product Category	Tools & Testers

Features

Material	Vinyl
maximum temperature	150
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Width	1
-------	---

Descriptions

Description	1.00" X 2.25" SELF-LAMINATING VINYL WIRE MARKER
extra long description	PAN S100X225VAM PXE™ S100X225VAM MP
Long Description	The S100X225VAM Die-Cut Self-Laminating Label Cassette includes both label material and ribbon for easy changeover. Self-laminating adhesive labels for wire/cable identification include a white print-on area and a clear overlaminates. For use with the MP300 printer. Vinyl. 1" x 2.25" (25.4 mm x 57.2 mm). Wire/Cable Size Range 8 - 4 AWG. Color Clear/White. 125 labels per cassette. 1 cassette per package.
Product Type	Pxe™ S100X225VAM MP Printer Self-Lam Label, Vinyl, White, 2.

Manufacturer Information

Brand	Panduit®
GTIN	00613056761377
Manufacturers Part Number	S100X225VAM
UPC	613056761377

Taxonomies, Classifications, and Categories

Type	Self-Laminating Label
------	-----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1904 Dutton Drive
78666-0000, TX San Marcos
Phone: 512-392-4310
Fax: 512-392-4390

Packaging

Carton	1
Weight Per each	0.204

Uses, Certifications, and Standards

standard	RoHS Compliant
----------	----------------