



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11581 5.5W Led PAR20 27K/3K/35K/4K/5K Enclosure Rated

Satco

Catalog Number	S11581
Manufacturer	Satco
Description	5.5 Watt PAR20 Led Medium Base - Silver Finish - CCT Selectable - 120 Volt - 40 Degree Beam Angle
Weight per unit	0.0500 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	E26
beam angle	40
dimmable	Yes-Dimmable
Lamp Type	LED
lumens	500
Power Factor	0.7
Voltage Rating	120
Wattage	5.5

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	2700/3000/3500/4000/5000

Descriptions

Description	5.5W LED PAR20 27K/3K/35K/4K/5K ENCLOSURE RATED
extra long description	SATCO S11581 5.5PAR20/LED/5CCT/FL/1
Long Description	5.5 Watt PAR20 LED Medium Base - Silver Finish - CCT Selectable - 120 Volt - 40 Degree Beam Angle
Product Type	5.5PAR20/Led/5CCT/FL/120V
Special Features	Warranty: 5-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +40C (+104F) ; Material: Polyamide (PA) ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Warm White to Natural Light ; Efficacy: 90.91 LPW ; Center Beam Candle Power: 884 ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: E26 ; Amps: 0.078A ; T24 Compliant: True

Manufacturer Information

Brand	Satco
GTIN	00045923115813
Manufacturers Part Number	S11581
UPC	045923115813



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED PAR SHAPE LAMPS
Type	LED Directional

Packaging

Carton	1
Package	6
Weight Per each	0.05

Uses, Certifications, and Standards

Application	LED
standard	cULus - Certified;cULus - Listed