



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12417 8W Led A19 40K Clear 800LM

Satco

| | |
|------------------|----------------------------------------------------------------|
| Catalog Number | S12417 |
| Manufacturer | Satco |
| Description | 8 Watt Led A19 Lamp - Clear Medium Base 4000K 90 Cri 120 Volts |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|-----------------|
| average life | 15000 |
| Base | E26 |
| beam angle | 320 |
| dimmable | Yes-Dimmable |
| lumens | 800 |
| Material | Glass; Aluminum |
| Power Factor | 0.7 |
| Shape | A19 |
| Voltage Rating | 120 |
| Warranty | 3 Year Limited |
| Wattage | 8 |

Material, Color, and Finish

| | |
|-----------------------------|-------|
| color rendering index (cri) | 90+ |
| color temperature | 4000 |
| Finish | Clear |

Dimensions and Weight

| | |
|------|------|
| Size | 4.02 |
|------|------|

Descriptions

| | |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 8W LED A19 40K CLEAR 800LM |
| extra long description | SATCO S12417 8A19/CL/LED/E26/940/12 |
| Long Description | 8 Watt LED A19 Lamp - Clear Medium Base 4000K 90 CRI 120 Volts |
| Product Type | 8A19/CL/Led/E26/940/120V |
| Special Features | Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Material: Aluminum / Glass ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Cool White ; Efficacy: 100.00 LPW ; Candle Power: 60 ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.067A |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923124174 |
| Manufacturers Part Number | S12417 |
| UPC | 045923124174 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
| Type | LED General Service |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight | 0.07 |
| Weight Per each | 1.5 |

Uses, Certifications, and Standards

| | |
|--------------------------------|-----------------------------------------------------------------------------|
| Application | LED |
| Operating Temperature standard | -20C (-4F) to a maximum of +45C (+113F) cULus - Certified;cULus - Listed |