



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S21274 5.5W Led C11 CNDLBR 30K

Satco

Catalog Number	S21274
Manufacturer	Satco
Description	5.5 Watt B11 Led Lamp - Clear - Candelabra Base - 90 Cri - 3000K - 120 Volts
Weight per unit	0.0700 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E12
beam angle	300
dimnable	Yes-Dimmable
lumens	500
Power Factor	0.74
Shape	B11
Voltage Rating	120
Wattage	5.5

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	3000
Finish	Clear

Dimensions and Weight

Size	3.4
------	-----

Descriptions

Description	5.5W LED C11 CNDLBR 30K
extra long description	SATCO S21274 5.5B11/LED/930/CL/120V
Long Description	5.5 Watt B11 LED Lamp - Clear - Candelabra Base - 90 CRI - 3000K - 120 Volts
Product Type	5.5B11/Led/930/CL/120V/E12
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: 120V only ; Material: Glass / Nickel Plated Aluminum ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Soft White ; Efficacy: 90.91 LPW ; DLC Approved: False ; FCC Compliant: True ; NSF Approved: No ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E12 ; Amps: 0.062A



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923205897
Manufacturers Part Number	S21274
UPC	045923205897

Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
Type	LED General Service

Packaging

Carton	1
Weight Per each	0.07

Uses, Certifications, and Standards

Application	LED
standard	cULus - Listed