



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S28737 20W Led A21 27K/5K/5K E26 120-277V 3000LM

Satco

| | |
|------------------|---|
| Catalog Number | S28737 |
| Manufacturer | Satco |
| Description | 20W Led A21 - High Lumen Output - 27K/40K/50K CCT Select - E26 Base - White - 120V-277V |
| Weight per unit | 0.6400 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|----------------|
| average life | 50000 |
| Base | E26 |
| beam angle | 280 |
| dimnable | Yes-Dimmable |
| lumens | 2760/3020/2860 |
| Power Factor | >0.9 |
| Voltage Rating | 120 to 277 |
| Wattage | 20 |

Material, Color, and Finish

| | |
|-----------------------------|----------------|
| color rendering index (cri) | 80+ |
| color temperature | 2700/4000/5000 |
| Finish | white |

Dimensions and Weight

| | |
|----------|------|
| Diameter | 2.46 |
| Length | 5.08 |

Descriptions

| | |
|------------------------|--|
| Description | 20W LED A21 27K/5K/5K E26 120-277V 3000LM |
| extra long description | SATCO S28737 20WA21/LED/3CCT/120-27 |
| Long Description | 20W LED A21 - High Lumen Output - 27K/40K/50K CCT Select - E26 Base - White - 120V-277V |
| Product Type | 20WA21/Led/3CCT/120-277V |
| Special Features | Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -25C (-13F) to +45C (+113F) ; Dimmable Text: 120V only ; Material: Die-Cast Aluminum / PC ; Indoor Outdoor: Indoor;Outdoor ; Surge Protection: Built-in surge protection - 2KV ; Color Temp: Warm White to Natural Light ; Efficacy: 138.00/151.00/143.00 LPW ; DLC Approved: False ; FCC Compliant: True ; NSF Approved: No ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: E26 ; Lamp Ballast Type AB: Type B ; Amps: 0.200A ; T24 Compliant: |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923287374 |
| Manufacturers Part Number | S28737 |
| UPC | 045923287374 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
| Type | LED HID Replacements |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.64 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------------|
| Application | LED |
| standard | cULus - Certified;cULus - Listed |