



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39012 4" 7W Led Retro 30K 450LM Dim Direct Wire (No Can)

Satco

Catalog Number	S39012
Manufacturer	Satco
Description	7 Watt Led Direct Wire Downlight - 3000K - 120 Volts - Dimmable
Weight per unit	0.5400 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

amperage rating	0.058
Ballast Type	Self
Lamp Included	Integrated
Lamp Type	LED
Material	METAL/PLASTIC
Number of Lamps	1
Reflector Type	Frost
Socket Type	Integrated
Voltage Rating	120 V
Warranty	5 Year Limited - Fixtures
Wattage	7

Material, Color, and Finish

Color	White / Frosted
Finish	White / Frosted
Style	Utility

Dimensions and Weight

Height	2.75
Length	5.69
Width	5.69

Descriptions

Description	4" 7W LED RETRO 30K 450LM DIM DIRECT WIRE (NO CAN)
extra long description	SATCO S39012 7WLED/DW/RDL/4/30K/120
Long Description	7 Watt LED Direct Wire Downlight - 3000K - 120 Volts - Dimmable
Product Type	7WLED/DW/RDL/4/30K/120V
Special Features	Amps: 0.058A;Beam Angle (degree): 100;Bulb Included: Integrated;Cct Selectable: False;Ceiling Aperture: 4.3125;Color Temp: Warm White;Incandescent Equivalent: 45W;Indoor Outdoor: Indoor;JA8 Compliant: True;Lens Finish: Frost;Lens Material: Plastic (PS);Location Rating: Wet;Mounting Procedure: Ceiling;Operating Frequency: 60Hz;Operating Temp: -20C (-4F) to +45C (+113F);Power Factor: 0.95;Replaceable Light Source: False;Style: Utility;Warranty: 5-Years;Wattage Selectable: False



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923390128
Manufacturers Part Number	S39012
UPC	045923390128

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED LIGHTING

Trade Size

aperture size	4.3125.
---------------	---------

Packaging

Carton	1
Package	12
Weight	0.37
Weight Per each	0.54

Uses, Certifications, and Standards

Application	Recessed
Frequency Rating	60 Hz
Mounting	CEILING
Operating Temperature standard	-20C (-4F) to a maximum of +45C (+113F) cETLus - Listed