

Eaton's Wiring Devices
Flush mount receptacles



Introducing
Eaton's upgraded
Flush Mount power
receptacles

Receptacles for today's
high amperage applications

EATON

Powering Business Worldwide

Eaton's new offering of flush mount power receptacles is specifically designed to meet the challenges of today's high amperage applications. From residential dryers and ranges to travel trailers and industrial welders, you can count on our products to deliver consistent, reliable power.




Heavy-duty flush mount receptacles

Product description

2-pole, 3-wire grounding; 3-pole, 3-wire non-grounding;
3-pole, 4-wire grounding
30A, 125V/AC, 250 V/AC, 125/250V/AC
50A, 250V/AC, 125/250V/AC

Design features


- Available in 4-wire configurations for new construction and 3-wire configurations for retrofit applications
- Heavy gauge steel mounting strap prevents accidental bending
- Single-plane terminal orientation for easy installation without needing tools at multiple angles
- Tri-combo terminal and mounting screws accept Slotted, Phillips, and Robertson-head tools for installation flexibility
- Part numbers and NEMA configurations are clearly visible for easy identification



Heavy-duty flush mount receptacles

Catalog no.	Description	Amps	Volts	Color suffix
<input type="checkbox"/> AH1233_	Heavy-duty flush mount power receptacle, NEMA 5-30R	30	125	BK
<input type="checkbox"/> AH1263_	Heavy-duty travel trailer power receptacle, NEMA TT-30R	30	125	BK
<input type="checkbox"/> AH1234_	Heavy-duty flush mount power receptacle, NEMA 6-30R	30	250	BK
<input type="checkbox"/> AH1254_	Heavy-duty flush mount power receptacle, NEMA 6-50R	50	250	BK, W
<input type="checkbox"/> AH38_	Heavy-duty dryer receptacle, NEMA 10-30R	30	125/250	BK, W
<input type="checkbox"/> AH32_	Heavy-duty range receptacle, NEMA 10-50R	50	125/250	BK, W
<input type="checkbox"/> AH1257_	Heavy-duty dryer receptacle, NEMA 14-30R	30	125/250	BK, W
<input type="checkbox"/> AH1167_	Heavy-duty dryer receptacle, Canadian mount, NEMA 14-30R	30	125/250	W
<input type="checkbox"/> AH1258_	Heavy-duty range receptacle, NEMA 14-50R	50	125/250	BK, W
<input type="checkbox"/> AH1168_	Heavy-duty range receptacle, Canadian mount, NEMA 14-50R	50	125/250	W

Product dimensions



Color Ordering Information

For ordering devices, include Cat. no. followed by the color suffix: BK (Black), W (White)



Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 178 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/wiringdevices