



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352



S49395 80W Led/Hid 50K Mogul Base

Satco

Catalog Number	S49395
Manufacturer	Satco
Description	80 Watt Led Hid Replacement - 5000K - Extended Mogul Base - Type B Ballast Bypass - Economy Hi-Pro
Weight per unit	3.4 (lbs/each)
Product Category	Lighting

Features

average life	35000
Base	EX39
beam angle	300
dimnable	Non-Dimmable
lumens	11040
Power Factor	>0.9
Shape	Corncob
Voltage Rating	120 to 277
Wattage	80

Material, Color, and Finish

color rendering index (cri)	80+
color temperature	5000
Finish	white

Dimensions and Weight

Size	8.69
------	------

Descriptions

Description	80W LED/HID 50K MOGUL BASE
extra long description	SATCO S49395 80W/LED/HP/850/100-277
Long Description	80 Watt LED HID Replacement - 5000K - Extended Mogul Base - Type B Ballast Bypass - Economy Hi-Pro
Product Type	80W/Led/HP/850/100-277V/Ex39
Special Features	Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -30C (-22F) to +50C (+122F) ; Material: Aluminum / Polycarbonate (PC) ; Indoor Outdoor: Indoor;Outdoor ; Surge Protection: Built-in surge protection - 4KV ; Color Temp: Natural Light ; Efficacy: 138.00 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: EX39 ; Lamp Ballast Type AB: Type B ; Amps: 0.800-0.289A ; T24 Compliant: False



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352

Manufacturer Information

Brand	Satco
GTIN	00045923493959
Manufacturers Part Number	S49395
UPC	045923493959

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	LED HID Replacements

Packaging

Carton	1
Weight Per each	3.36

Uses, Certifications, and Standards

Application	LED
standard	cULus - Certified;cULus - Classified;cULus - Listed