



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S62010CT00 2" SS316 Rigid Conduit, 10' W/Coupling

Cablofil

Catalog Number	S62010CT00
Manufacturer	Cablofil
Description	Rigid Conduit, 316 Stainless Steel Material; Bright Polished Finish; 10 FT; 2.067 Inch Inner Diameter; 2.375 Inch Outer Diameter; UL/Cul 6A, Csa C22.1 Approval; Ansi/Nfpa 70, Nec Applicable Standard; 3.5 LB Per FT Weight; 2 Inch Trade Size
Weight per unit	3.5 (lbs/each)
Product Category	Galvanized Heavy Wall Conduit

Features

Applicable Standard	ANSI/NFPA 70, NEC
End Style	Threaded
Material	316 Stainless Steel

Material, Color, and Finish

Finish	Bright Polished
--------	-----------------

Dimensions and Weight

Inner Diameter	2.067 Inch
Length	10 ft
Outer Diameter	2.375 INCH

Descriptions

Additional Information	Thread Size 11.5 TPI
Commodity Description	Galvanized Rigid Steel Conduit
Description	2" SS316 RIGID CONDUIT, 10' W/COUPLING
extra long description	316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FT; 2.067 INCH INNER DIAMETER; 2.375 INCH OUTER DIAMETER; UL/CUL 6A, CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC APPLICABLE STANDARD; 2 INCH TRADE SIZE; THREADED END STYLE; CALBRITE BRAND; THREAD SIZE 11.5 TPI; WEIGHT 3.5 LB PER FT
Long Description	RIGID CONDUIT, 316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FT; 2.067 INCH INNER DIAMETER; 2.375 INCH OUTER DIAMETER; UL/CUL 6A, CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC APPLICABLE STANDARD; 3.5 LB PER FT WEIGHT; 2 INCH TRADE SIZE
Product Type	Rigid Conduit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	CALPIPE INDUSTRIES, INC.
GTIN	00847656000158
Manufacturers Part Number	S62010CT00
UPC	847656000158

Taxonomies, Classifications, and Categories

Category Description	Stainless Rigid Conduit
----------------------	-------------------------

Trade Size

Trade Size	2 INCH
------------	--------

Availability

Status	Inactive
--------	----------

Packaging

Carton	10
Weight	3.5 Lb per Ft
Weight Per each	3.5

Uses, Certifications, and Standards

Approval	UL/CUL 6A, CSA C22.1
----------	----------------------