



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636



S60710CT00 3/4" SS316 Rigid Conduit, 10' W/Coupling

Cablofil

Catalog Number	S60710CT00
Manufacturer	Cablofil
Description	Rigid Conduit, 316 Stainless Steel Material; Bright Polished Finish; 10 FT; 0.824 Inch Inner Diameter; 1.05 Inch Outer Diameter; UL/Cul 6A, Csa C22.1 Approval; Ansi/Nfpa 70, Nec Applicable Standard; 1.09 LB Per FT Weight; 3/4 Inch Trade Size
Weight per unit	1.1 (lbs/each)
Product Category	Galvanized Heavy Wall Conduit

Features

Applicable Standard	ANSI/NFPA 70, NEC
End Style	Threaded
Material	316 Stainless Steel

Material, Color, and Finish

Finish	Bright Polished
--------	-----------------

Dimensions and Weight

Inner Diameter	0.824 Inch
Length	10 ft
Outer Diameter	1.05 INCH

Descriptions

Additional Information	Thread Size 14 TPI
Commodity Description	Galvanized Rigid Steel Conduit
Description	3/4" SS316 RIGID CONDUIT, 10' W/COUPLING
extra long description	316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FT; 0.824 INCH INNER DIAMETER; 1.05 INCH OUTER DIAMETER; UL/CUL 6A, CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC APPLICABLE STANDARD; 3/4 INCH TRADE SIZE; THREADED END STYLE; CALBRITE BRAND; THREAD SIZE 14 TPI; WEIGHT 1.09 LB PER FT
Long Description	RIGID CONDUIT, 316 STAINLESS STEEL MATERIAL; BRIGHT POLISHED FINISH; 10 FT; 0.824 INCH INNER DIAMETER; 1.05 INCH OUTER DIAMETER; UL/CUL 6A, CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC APPLICABLE STANDARD; 1.09 LB PER FT WEIGHT; 3/4 INCH TRADE SIZE
Product Type	Rigid Conduit



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636

Manufacturer Information

Brand	CALPIPE INDUSTRIES, INC.
GTIN	00847656000110
Manufacturers Part Number	S60710CT00
UPC	847656000110

Taxonomies, Classifications, and Categories

Category Description	Stainless Rigid Conduit
----------------------	-------------------------

Trade Size

Trade Size	3/4 INCH
------------	----------

Availability

Status	Inactive
--------	----------

Packaging

Carton	10
Weight	1.09 Lb per Ft
Weight Per each	1.09

Uses, Certifications, and Standards

Approval	UL/CUL 6A, CSA C22.1
----------	----------------------